


Data sheet for SINAMICS G120X

Article No.: 6SL3220-3YE48-0AP0

Client order no. : Order no. : Offer no. : Remarks :



Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications	
Power factor λ	0.90 0.95
Offset factor $\cos\phi$	0.99
Efficiency η	0.98
Sound pressure level (1m)	72 dB
Power loss 3)	3.160 kW
Filter class (integrated)	RFI suppression filter for Category C2
EMC category (with accessories)	Category C2
Safety function "Safe Torque Off"	without
_	

_		
Commu	ınıca	tion
COIIIII	ııııca	LIVII

Communication PROFIBUS DP



Item no. : Consignment no. : Project :

Inputs /	outputs	
Standard digital inputs		
Number	6	
Switching level: $0 \rightarrow 1$	11 V	
Switching level: $1 \rightarrow 0$	5 V	
Max. inrush current	15 mA	
Fail-safe digital inputs		
Number	1	
Digital outputs		
Number as relay changeover contact	2	
Output (resistive load)	DC 30 V, 5.0 A	
Number as transistor	0	
Analog / digital inputs		
Number	2 (Differential input)	
Resolution	10 bit	
Switching threshold as digital input		
0 → 1	4 V	
1 → 0	1.6 V	
Analog outputs		
Number	1 (Non-isolated output)	

PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5\,^{\circ}\text{C}$

Closed-loop control techniques	
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No




Data sheet for SINAMICS G120X

Article No.: 6SL3220-3YE48-0AP0

Ambie	ent conditions	
Standard board coating type	Class 3C2, according to IEC 60721-3-3: 2002	
Cooling	Air cooling using an integrated fan	
Cooling air requirement	0.153 m³/s (5.403 ft³/s)	
Installation altitude	1,000 m (3,280.84 ft)	
Ambient temperature		
Operation	-20 45 °C (-4 113 °F)	
Transport	-40 70 °C (-40 158 °F)	
Storage	-25 55 °C (-13 131 °F)	
Relative humidity		
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible	
Co	nnections	
Signal cable		
Conductor cross-section	0.15 1.50 mm ² (AWG 24 AWG 16)	
Line side		
Version	M10 screw	
Conductor cross-section	35.00 2 x 120.00 mm ² (AWG 1 AWG 2 x 4/0)	
Motor end		
Version	M10 screw	
Conductor cross-section	35.00 2 x 120.00 mm ² (AWG 1 AWG 2 x 4/0)	
DC link (for braking resistor)		
PE connection	M10 screw	
Max. motor cable length		
	150 m (492.13 ft)	
Shielded	130 111 (492.13 11)	

	Mechan	ical data	
Degree of protection		IP20 / UL open type	
Frame size		FSF	
Net weight		71 kg (156.53 lb)	
Dimensions			
	Width	305 mm (12.01 in)	
	Height	709 mm (27.91 in)	
	Depth	369 mm (14.53 in)	
_			
Standards			
C	ompliance with standards	UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH	
CE marking		EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC	

Converter losses to IEC61800-9-2*	
Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	44.6 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

 $^{^{1)}\}mbox{The}$ output current and HP ratings are valid for the voltage range 440V-480V

³⁾ Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.



Data sheet for SINAMICS G120X

Article No.: 6SL3220-3YE48-0AP0

	Operator panel: I	ntelligent Operator Panel (IOP-2)
	Screen	
Display design	LCD color	Ambient temperature
Screen resolution	320 x 240 Pixel	Operation
	Mechanical data	Storage
Degree of protection	IP55 / UL type 12	Transport
Net weight	0.134 kg (0.30 lb)	Relative humidity at 25°C
Dimensions		Max. operation
Width	70.00 mm (2.76 in)	
Height	106.85 mm (4.21 in)	
Depth	19.65 mm (0.77 in)	Certificate of suitability

Ambient conditions		
Ambient temperature		
Operation	0 50 °C (32 122 °F)	
	55 °C only with door installation kit	
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
Relative humidity at 25°C during		
Max. operation	95 %	
Ammuniala		
Approvals		
Certificate of suitability	CE, cULus, EAC, KCC, RCM	