

Data sheet for SINAMICS G120X

Article No.: 6SL3220-3YH42-0UP0

Client order no. : Order no.: Offer no. : Remarks:

ıuata	Rated data		
3 AC			
500 690 V +10 %	-20 %		
47 63 Hz			
690V IEC	600V NEC		
78.00 A	78.00 A		
66.40 A	66.40 A		
3 AC			
690V IEC	600V NEC 1)		
75.00 kW	75.00 hp		
55.00 kW	60.00 hp		
80.00 A	80.00 A		
62.00 A	62.00 A		
82.00 A			
108.00 A			
2 kHz			
0 200 Hz			
0 550 Hz			
	500 690 V +10 % 47 63 Hz 690V IEC 78.00 A 66.40 A 3 AC 690V IEC 75.00 kW 55.00 kW 80.00 A 62.00 A 108.00 A 2 kHz 0 200 Hz		

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

Communication

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications	
Power factor λ	0.90 0.95
Offset factor $\cos\phi$	0.99
Efficiency η	0.98
Sound pressure level (1m)	72 dB
Power loss 3)	1.410 kW
Filter class (integrated)	Unfiltered
EMC category (with accessories)	without
Safety function "Safe Torque Off"	without SIRIUS device (e.g. via S7- 1500F)

Communication PROFIBUS DP



Item no.: Consignment no. : Project :

Inputs / outputs		
Standard digital inputs		
Number	6	
Switching level: $0 \rightarrow 1$	11 V	
Switching level: $1 \rightarrow 0$	5 V	
Max. inrush current	15 mA	
Fail-safe digital inputs		
Number	1	
Digital outputs		
Number as relay changeover contact	2	
Output (resistive load)	DC 30 V, 5.0 A	
Number as transistor	0	
Analog / digital inputs		
Analog / digital inputs Number	2 (Differential input)	
<u> </u>	2 (Differential input) 10 bit	
Number		
Number Resolution		
Number Resolution Switching threshold as digital input	10 bit	
Number Resolution Switching threshold as digital input 0 → 1	10 bit 4 V	
Number Resolution Switching threshold as digital input $0 \rightarrow 1$ $1 \rightarrow 0$	10 bit 4 V	

PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5~^\circ\text{C}$

Closed-loop control techniques	
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No




Data sheet for SINAMICS G120X

Article No.: 6SL3220-3YH42-0UP0

Ambient conditions	
Standard board coating type	Class 3C2, according to IEC 60721-3-3: 2002
Cooling	Air cooling using an integrated fan
Cooling air requirement	0.153 m³/s (5.403 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
Ambient temperature	
Operation	-20 45 °C (-4 113 °F)
Transport	-40 70 °C (-40 158 °F)
Storage	-25 55 °C (-13 131 °F)
Relative humidity	
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible
Conne	ections
Signal cable	
Conductor cross-section	0.15 1.50 mm ² (AWG 24 AWG 16)
Line side	
Version	M10 screw
Conductor cross-section	35.00 2 x 120.00 mm ² (AWG 1 AWG 2 x 4/0)
Motor end	
Version	M10 screw
Conductor cross-section	35.00 2 x 120.00 mm ² (AWG 1 AWG 2 x 4/0)
DC link (for braking resistor)	
PE connection	M10 screw
Max. motor cable length	
Shielded	300 m (984.25 ft)
Unshielded	450 m (1,476.38 ft)

Mechanical data	
Degree of protection	IP20 / UL open type
Frame size	FSF
Net weight	61 kg (134.48 lb)
Dimensions	
Width	305 mm (12.01 in)
Height	709 mm (27.91 in)
Depth	369 mm (14.53 in)
Standards	
Compliance with standards	UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH
CE marking	EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC

Converter losses to IEC61800-9-2*	
Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	31.5 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

 $^{^{1)}\}mbox{The}$ output current and HP ratings are valid for the voltage range 550V-600V

³⁾ Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.



Data sheet for SINAMICS G120X

Article No.: 6SL3220-3YH42-0UP0

	Operator panel: I	ntelligent Operator Panel (IOP-2)
	Screen	
Display design	LCD color	Ambient temperature
Screen resolution	320 x 240 Pixel	Operation
	Mechanical data	Storage
Degree of protection	IP55 / UL type 12	Transport
Net weight	0.134 kg (0.30 lb)	Relative humidity at 25°C
Dimensions		Max. operation
Width	70.00 mm (2.76 in)	operation
Height	106.85 mm (4.21 in)	
Depth	19.65 mm (0.77 in)	Certificate of suitability

Ambient conditions Ambient temperature	
	55 °C only with door installation kit
Storage	-40 70 °C (-40 158 °F)
Transport	-40 70 °C (-40 158 °F)
Relative humidity at 25°C during	
Max. operation	95 %
	Annyovala
	Approvals
Certificate of suitability	CE, cULus, EAC, KCC, RCM