ت الت الت الت الت الت الت الت الت الت ال	т (П	D	0	Φ	A	
	ØS					
			LAYOUT SHOWN AS	EXAMPLE		
	Keying Shown as example					
CHARACTERISTICS	Connector dimension]				
-Standard : Based on MIL-DTL-38999 Series III	Dim Nominal ØS 29.4 Max]				
-Shell Material : Composite -Shell Plating : Nickel -Insulator : Thermoplastic	Z' 31.5 Max VV THREAD M18x1-6g]	SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)			
-Contacts : Copper Alloy -Seals & Grommet : Silicon Elastomer			Count	try Jurisdiction & Contra	ol List	
-Contact Plating : Gold over copper Alloy 0.8µm minimum			Country Jurisdiction & Control List FR Not Listed			
-Durability : 500 Mating cycles -Delivered without Souriau contacts			PN: 8D513M35SNL			
-Temperature Range65°C to +200°C						
-Salt Spray : 2000 hours		A 18-10-20	16 First Release			
Mass : 17.6 g ± 10%		ISS DATE			MOD N ^o	۷°
			Designed By: Date: CUSTOMER DRAWING TITLE Composite Plug 8D series		DRAWING	
		TITLE				
BASIC SERIES: 8D 5 - 13 N SHELL TYPE : Plug with RFI Shielding	A 35 S N L Delivered W	/O Contacts NA	General linear Tolerances:	NPRDS / F 85		
CONTACT TYPE : Standard Crimp Contact			U WWW.SOURIAU.	COM it must	ment is the property of SOURIAU not be reproduced or	
SHELL SIZE : 13	CONTACT TYPE : SOCKET(5				ated without permission	
PLATING : M = Nickel	CONTACT LAY	OUT : 13-35 A3	SOURIAL 8D513M		SHEET	
					1 1//	

r	т	G	г – – –	m	U	0	
		Contact Layout					
4	-x ·	$\begin{array}{c} \bullet \\ \bullet $					
	2 +.126 (3.20) 3 +.182 (4.62) 4 +.203 (5.16) 5 +.182 (4.62) 6 +.126 (3.20) 7 +.045 (1.14)	Y-axis (mm) position ID X-axis (mm) Y-axis (mm) +.197 (5.00) 12 182 (4.62) +.088 (2.24) +.158 (4.01) 13 126 (3.20) +.158 (4.01) +.088 (2.24) 14 045 (1.14) +.197 (5.00) +.000 (0.00) 15 +.045 (1.14) +.107 (2.72) 088 (2.24) 16 +.117 (2.97) +.026 (0.66) 158 (4.01) 17 +.093 (2.36) 075 (1.91) 197 (5.00) 18 +.000 (.00) 120 (3.05)					
ω	(Sheli Arrangement Nuu size no. co	-197 (5.00) 19 -093 (2.36) -075 (1.91) 158 (4.01) 20 117 (2.97) +.026 (0.66) 088 (2.24) 21 045 (1.14) +.107 (2.72) +.000 (0.00) 22 +.000 (.00) 030 (0.76) Applicable to MIL-DTL-38999 only) 045 (1.14) +.07 (2.72) mber of Size Service Contact Superseder 22 22D M All MS27527-3					
						SOURIAU shall not be liab due to a use of the Pro the Specifications issued by (professional recon	ducts w either c
N						PN: 8D5	Count FR 513N
					A 18-10-20 ISS DATE Designed By:	16 First Release Latest modification - by Date:	
-					SCALE NA	Genera Tolera ±	ances:
					SOURIA		
					FORMAT A3	SOU 8D5:	
_	Н	G	F	E	D	C	

