


Data sheet for SINAMICS G120X

6SL3230-2YH26-0UF0 Article No.:

Client order no. : Order no.: Offer no. : Remarks :



Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
0.90 0.95		
0.99		
0.97		
70 dB		
0.360 kW		
Unfiltered		
without		
without SIRIUS device (e.g. via S7- 1500F)		

Communication

PROFINET, EtherNet/IP Communication



Item no.: Consignment no. : Project :

Inputs / outputs		
Standard digital inputs		
Number	6	
Switching level: $0 \rightarrow 1$	11 V	
Switching level: $1 \rightarrow 0$	5 V	
Max. inrush current	15 mA	
Fail-safe digital inputs		
Number	1	
Digital outputs		
Number as relay changeover contact	2	
Output (resistive load)	DC 30 V, 5.0 A	
Number as transistor	0	
Analog / digital inputs		
Number	2 (Differential input)	
Resolution	10 bit	
Switching threshold as digital input		
0 → 1	4 V	
1 → 0	1.6 V	
Analog outputs		

PTC/ KTY interface

Number

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy ±5 °C

1 (Non-isolated output)

Closed-loop control techniques		
V/f linear / square-law / parameterizable	Yes	
V/f with flux current control (FCC)	Yes	
V/f ECO linear / square-law	Yes	
Sensorless vector control	Yes	
Vector control, with sensor	No	
Encoderless torque control	No	
Torque control, with encoder	No	



Data sheet for SINAMICS G120X

Article No.: 6SL3230-2YH26-0UF0


Ambient	conditions
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002
Cooling	Air cooling using an integrated fan
Cooling air requirement	0.055 m³/s (1.942 ft³/s)
Installation altitude	1,000 m (3,280.84 ft)
Ambient temperature	
Operation	-20 45 °C (-4 113 °F)
Transport	-40 70 °C (-40 158 °F)
Storage	-25 55 °C (-13 131 °F)
Relative humidity	
Max. operation	$95~\%$ At $40~^\circ\text{C}$ (104 $^\circ\text{F}$), condensation and icing not permissible
Conn	ections
Signal cable	
Conductor cross-section	0.15 1.50 mm ² (AWG 24 AWG 16)
Line side	
Version	screw-type terminal
Conductor cross-section	10.00 35.00 mm ² (AWG 8 AWG 2)
Motor end	
Version	Screw-type terminals
Conductor cross-section	10.00 35.00 mm ² (AWG 8 AWG 2)
DC link (for braking resistor)	
PE connection	Screw-type terminals
Max. motor cable length	
	200 (656.47.6)
Shielded	200 m (656.17 ft)

Mechanical data		
Degree of protection	IP20 / UL open type	
Frame size	FSD	
Net weight	16.6 kg (36.60 lb)	
Dimensions		
Width	200 mm (7.87 in)	
Height	472 mm (18.58 in)	
Depth	248 mm (9.76 in)	
Standards		
Compliance with standards	UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH	
CE marking	EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC	

Converter losses to IEC61800-9-2*

IE2

41.5 %



The percentage values show the losses in relation to the rated apparent power of the converter.

50%

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

Efficiency class

Comparison with the reference converter (90% / 100%)

 $^{^{\}rm 1)} The \ output \ current \ and \ HP \ ratings \ are \ valid \ for \ the \ voltage \ range \ 550 V-600 V$

³⁾Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.



Data sheet for SINAMICS G120X

Article No.: 6SL3230-2YH26-0UF0

	Operator pane	el: Basic Operator Panel (BOP-2)
	Screen	
Display design	LCD, monochrome	Ambient temperature
	Mechanical data	Operation
Degree of protection	IP55 / UL type 12	Storage
Net weight	0.140 kg (0.31 lb)	Transport Relative humidity at 25
Dimensions		Max. operation
Width	70.00 mm (2.76 in)	wax. operation
Height	106.85 mm (4.21 in)	
Depth	19.60 mm (0.77 in)	Certificate of suitability

	<u> </u>		
Ambient conditions			
Ambient temperature			
Operation	0 50 °C (32 122 °F)		
Storage	-40 70 °C (-40 158 °F)		
Transport	-40 70 °C (-40 158 °F)		
Relative humidity at 25°C during			
Max. operation	95 %		
Approvals			
Certificate of suitability	CE, cULus, EAC, KCC, RCM		