			0	₩	Þ
	25				
	Keying Shown as example		LAYOUT SHOWN AS	EXAMPLE	
CHARACTERISTICS -Standard : Based on MIL-DTL-38999 Series III -Shell Material : Composite -Shell Plating : Nickel -Insulator : Thermoplastic -Contacts : Copper Alloy -Seals & Grommet : Silicon Elastomer Contact Plating : Cold over conner Alloy 0.8µm minimum	Connector dimensionDimNominalØS41.7 MaxZ'31.5 MaxVV THREADM31x1-6g		SOURIAU shall not be liable for a due to a use of the Products w the Specifications issued by either (professional recommend	which does not comply with of the Parties or by a third party ation, technical notice.) htry Jurisdiction & Contr	
-Durability : 500 Mating cycles -Delivered with Souriau contacts and Accessories -Temperature Range : -65°C to +200°C		A 08-10-2016	FF PN: 8D521		
-Salt Spray : 2000 hours - Mass : 62.4 g ± 10%		ISS DATE Designed By:	Latest modification - by Date:	CUSTOMER	MOD N
		TITLE Composite Plug 8D series			
BASIC SERIES: 8D 5 - 21 M SHELL TYPE : Plug with RFI Shielding	48 B N ORIENTATION :	NA SOURIAU	General linear Tolerances: ± WWW.SOURIAU.	CONA	
CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 21	CONTACT TYPE : SOCKET(500 Mating				cated without permission

	т	۵	н г	т	0	
		Contact Layout				
		48				
4	×-					

F

Е

G

Н


4#8 Power

21-48				
Ctc	x	Y		
Α	4.57	4.57		
В	4.57	-4.57		
С	-4.57	-4.57		
D	-4.57	4.57		
B C	4.57 -4.57	-4.57 -4.57		

ယ

 \sim

SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.) Country FR PN: 8D521M48BN 08-10-2016 First Release А DATE Latest modification - by ISS Designed By: Date: TITLE SCALE General linear $(\bigcirc$ Tolerances: NA ±---**SOURIAU** WWW.SOURIAU.COM FORMAT A3 С D



 \succ

ω