3RA2110-0BA15-1AK6

Data sheet



FUSELESS LOAD FEEDER DIRECT START, AC 400V, SZ. S00 0.14...0.2A, AC110/120V 50/60HZ SCREW TERMINAL FOR RAIL MOUNTING, TYPE OF ASSIGNMENT 2,IQ = 150KA (ALSO FULFILLS TYPE OF ASSIGNMENT 1) 1NO (CONTACTOR)

product brand name	SIRIUS			
product designation	non-fused load feeders 3RA2			
design of the product	direct starter			
manufacturer's article number				
 of the supplied contactor 	3RT2015-1AK61			
 of the supplied circuit-breakers 	3RV2011-0BA10			
 of the supplied link module 	3RA1921-1DA00			
General technical data				
size of the circuit-breaker	S00			
size of load feeder	S00			
product extension auxiliary switch	Yes			
insulation voltage with degree of pollution 3 at AC rated value	690 V			
degree of pollution	3			
surge voltage resistance rated value	6 kV			
shock resistance according to IEC 60068-2-27	6g / 11 ms			
mechanical service life (switching cycles) of contactor typical	30 000 000			
type of assignment	2			
Substance Prohibitance (Date)	10/01/2009			
Ambient conditions				
ambient temperature				
 during operation 	-20 +60 °C			
 during storage 	-50 +80 °C			
e during transport	E0			
during transport	-50 +80 °C			
during transport Main circuit	-50 +80 ℃			
	3			
Main circuit				
Main circuit number of poles for main current circuit	3			
Main circuit number of poles for main current circuit design of the switching contact adjustable current response value current of the	3 electromechanical			
Main circuit number of poles for main current circuit design of the switching contact adjustable current response value current of the current-dependent overload release	3 electromechanical			
Main circuit number of poles for main current circuit design of the switching contact adjustable current response value current of the current-dependent overload release operating voltage	3 electromechanical 0.14 0.2 A			
Main circuit number of poles for main current circuit design of the switching contact adjustable current response value current of the current-dependent overload release operating voltage • rated value	3 electromechanical 0.14 0.2 A			
Main circuit number of poles for main current circuit design of the switching contact adjustable current response value current of the current-dependent overload release operating voltage • rated value • at AC-3 rated value maximum	3 electromechanical 0.14 0.2 A 690 V 690 V			
Main circuit number of poles for main current circuit design of the switching contact adjustable current response value current of the current-dependent overload release operating voltage • rated value • at AC-3 rated value maximum operating frequency rated value	3 electromechanical 0.14 0.2 A 690 V 690 V 50 60 Hz			
Main circuit number of poles for main current circuit design of the switching contact adjustable current response value current of the current-dependent overload release operating voltage • rated value • at AC-3 rated value maximum operating frequency rated value operational current at AC-3 at 400 V rated value	3 electromechanical 0.14 0.2 A 690 V 690 V 50 60 Hz			
Main circuit number of poles for main current circuit design of the switching contact adjustable current response value current of the current-dependent overload release operating voltage • rated value • at AC-3 rated value maximum operating frequency rated value operational current at AC-3 at 400 V rated value operating power at AC-3 • at 400 V rated value • at 500 V rated value	3 electromechanical 0.14 0.2 A 690 V 690 V 50 60 Hz 0.2 A 60 W 60 W			
Main circuit number of poles for main current circuit design of the switching contact adjustable current response value current of the current-dependent overload release operating voltage • rated value • at AC-3 rated value maximum operating frequency rated value operational current at AC-3 at 400 V rated value operating power at AC-3 • at 400 V rated value	3 electromechanical 0.14 0.2 A 690 V 690 V 50 60 Hz 0.2 A			

General Product Approval		ous locations	Conformity
		For use in hazard-	Declaration of
Certificates/ approvals	inger-saie, for vertical conta	act north the front	
60529 touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front		
according to SN 31920 protection class IP on the front according to IEC	IP20		
proportion of dangerous failures with high demand rate	73 %		
B10 value with high demand rate according to SN 31920	1 000 000		
connectable conductor cross-section for main contacts finely stranded with core end processing Safety related data	0.5 2.5 mm²		
at AWG cables for main contacts	2x (20 16), only for contactor 2x (18 14), 2x 12		
for main contacts stranded AWC cables for main contacts	0.5 4 mm², 2x (0.75 2.5 mm²)		
type of connectable conductor cross-sections			
type of electrical connection for main current circuit	screw-type terminals		
Connections/ Terminals	, , , ,		
— at the side	9 mm		
— upwards — downwards	20 mm		
	0 mm 20 mm		
— forwards — backwards	0 mm 0 mm		
for live parts — forwards	0 mm		
	10 mm		
— at the side — downwards			
— upwards — at the side	20 mm 9 mm		
	0 mm		
— forwards — backwards	0 mm		
for grounded parts— forwards	0 mm		
required spacing			
depth	97.1 mm		
width	45 mm		
height	167.2 mm		
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail		
mounting position	vertical		
Installation/ mounting/ dimensions			
at 500 V according to IEC 60947-4-1 rated value	100 000 A		
at 400 V according to IEC 60947-4-1 rated value at 500 V according to IEC 60947-4-1 rated value	153 000 A		
at 690 V according to IEC 60947-4-1 rated value at 400 V according to IEC 60947-4-1 rated value	100 000 A		
conditional short-circuit current (Iq)	400 000 1		
design of the short-circuit trip	magnetic		
product function short circuit protection	Yes		
Short-circuit protection			
unit			
response value current of instantaneous short-circuit trip	2.6 A		
design of the overload release	thermal (bimetallic)		
trip class	CLASS 10		
Protective and monitoring functions			
apparent holding power of magnet coil at AC	4.2 VA		
at 60 Hz rated value	120 V		
at 50 Hz rated value	110 V		
control supply voltage at AC			



Confirmation



EAC





Declaration of Conformity

Test Certificates

Marine / Shipping



Special Test Certific-<u>ate</u>

Type Test Certificates/Test Report







Marine / Shipping other Railway









Confirmation

Vibration and Shock

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2110-0BA15-1AK6

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2110-0BA15-1AK6

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RA2110-0BA15-1AK6

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb= =3RA2110-0BA15-1AK6&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RA2110-0BA15-1AK6/char

Further characteristics (e.g. electrical endurance, switching frequency)
http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2110-0BA15-1AK6&objecttype=14&gridview=view1

12/15/2020 last modified: