	ד <u>ס</u> ד	m	D	0	B	
4	R 22.6 Max () () () () () () () () () () () () ()	S		<image/> <image/>		4
		nown as example				
	CHARACTERISTICS -Standard : Based on MIL-DTL-38999 Series III -Shell Material : Aluminium -Shell Plating : Olive drab Cadmium -Insulator : Thermoplastic -Contacts : Copper Alloy	Connector dimension Dim Nominal A 34.9±0.3 B 19.07+0.1/-0.15 R 32.5Max S 31.8±0.4 W 2.2+0.9/-0.1 VV THREAD M15x1-6g		SOURIAU shall not be liable for any nor due to a use of the Products which d the Specifications issued by either of the (professional recommendation, t	oes not comply with Parties or by a third party	
N	-Seals & Grommet: Silicon Elastomer-Contact Plating: Gold over copper Alloy 0.8μm minimum-Durability: 500 Mating cycles-Delivered with Souriau contacts and Accessories	,		PN: 8D711W99	Jurisdiction & Control List Not Listed	2
	-Delivered with Souriau contacts and Accessories -Temperature Range : -65°C to +175°C -Salt Spray : 500 hours -Mass : 18.06 g ± 10%		A 01-10-2016	First Release Latest modification - by	MOD N°	
	-Wass . 18.00 g ± 10%		Designed By:	Date:	customer drawing	-
<u> </u>	BASIC SERIES: 8D 7 - 11 W 99 A SHELL TYPE : Jam nut Receptacle Image: Second	N	SCALE	General linear Tolerances: ±	NPRDS / PROJECT 859	1
	CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 11	ORIENTATION : N CONTACT TYPE : PIN(500 Matings)	SOURIAU	WWW.SOURIAU.CON	This document is the property of SOURIAU it must not be reproduced or communicated without permission	
	PLATING : W = Olive drab Cadmium	CONTACT LAYOUT : 11-99	FORMAT A3	SOURIAU DE 8D711W99		
	H G F	E V	D	C	ВІА	

ſ	т <u>G</u> т	ш	D C B A	
4	Contact Layout $f \xrightarrow{F} A \oplus f \oplus f \xrightarrow{F} A \oplus f \oplus g \xrightarrow{F} A \oplus g \xrightarrow{F} A \oplus g \xrightarrow{F} A \oplus g \xrightarrow{F} $		Panel cutout JAM NUT RECEPTACLE (TYPE 7)	4
	$\begin{tabular}{ c c c c c } \hline Contacts & (Insert arrangement 11-99) & \hline Contact arrangement 11-99) & \hline Contact position & Location & \hline D & (mm) & C & +.065 (1.65) & +.113 (2.87) & \hline D &065 (1.65) &113 (2.87) & \hline D &065 (1.65) &113 (2.87) & \hline D &065 (1.65) & +.113 (2.87) & \hline E &130 (3.30) & +.000 (0.00) & \hline F &065 (1.65) & +.113 (2.87) & \hline G & +.000 (0.00) & \hline F &065 (1.65) & +.113 (2.87) & \hline G & +.000 (0.00) & \hline \hline Shell & Arrangement & Number of & Size & Service & Contact & Supersedes & \hline \hline no. & contacts & contacts & rating & location & \hline \hline \end{tabular}$			_
ى	sizeno.contactsratinglocation11-99720IAliMS20050-99		Dim Nominal B 19.59+0/-0.25 ØC 20.96+0.25/-0	3
			SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)	
2			Country Jurisdiction & Control List PR Not Listed PN: 8D711W99AN A 01-10-2016 First Release First Release </td <td>2</td>	2
			ISS DATE Latest modification - by MOD N° Designed By: Date: CUSTOMER DRAWING	_
			TITLE Aluminium Receptacle 8D series SCALE General linear Tolerances: NPRDS / PROJECT	
<u> </u>			NA ± 859 SOURIAU WWW.SOURIAU.COM This document is the property of SOURIAU it must not be reproduced or communicated without permission	1
			FORMATSOURIAU DRG N°SHEETA38D711W99AN-C2/2	
	H G F I	E	D C B A	