## 3RA2220-4BB27-0AP0

**Data sheet** 



Load feeder fuseless, Reversing duty 400 V AC, Size S0 13.0...20.0 A 230 V AC screw terminal for installation on standard mounting rail with standard mounting rail adapter (also fulfills type of coordination 1) Type of coordination 2, Iq = 150 kA 1 NO+1 NC (contactor)

product brand name	SIRIUS		
product designation	Reversing starter		
design of the product	for standard rail or screw mounting		
product type designation	3RA22		
manufacturer's article number			
<ul> <li>of the supplied contactor</li> </ul>	3RT2027-1AP00		
<ul> <li>of the supplied circuit-breakers</li> </ul>	3RV2021-4BA10		
<ul> <li>of the supplied RH assembly kit</li> </ul>	3RA2923-1BB1		
<ul> <li>of the supplied link module</li> </ul>	3RA2921-1AA00		
General technical data			
size of the circuit-breaker	S0		
size of load feeder	S0		
insulation voltage with degree of pollution 3 at AC rated value	690 V		
surge voltage resistance rated value	6 kV		
degree of protection NEMA rating	other		
shock resistance according to IEC 60068-2-27	6g / 11 ms		
mechanical service life (switching cycles) of contactor typical	10 000 000		
type of assignment	2		
type of protection according to ATEX directive 2014/34/EU	Ex II (2) GD		
certificate of suitability according to ATEX directive 2014/34/EU	DMT 02 ATEX F 001		
Substance Prohibitance (Date)	10/01/2009		
Ambient conditions			
ambient temperature			
<ul> <li>during operation</li> </ul>	-20 +60 °C		
<ul> <li>during storage</li> </ul>	-50 +80 °C		
during transport	-50 +80 °C		
temperature compensation	-20 +60 °C		
relative humidity during operation	10 95 %		
Main circuit			
number of poles for main current circuit	3		
design of the switching contact	electromechanical		
adjustable current response value current of the current-dependent overload release	13 20 A		
operating voltage			
• rated value	690 V		
<ul> <li>at AC-3 rated value maximum</li> </ul>	690 V		

operating frequency rated value	50 60 Hz			
operating frequency rated value operational current at AC-3 at 400 V rated value	15.5 A			
operating power at AC-3				
• at 400 V rated value	7 500 W			
Control circuit/ Control	7 000 11			
type of voltage of the control supply voltage	AC			
control supply voltage at AC				
at 50 Hz rated value	230 V			
at 50 Hz rated value     at 50 Hz rated value	230 v 230 230 V			
apparent holding power of magnet coil at AC	9.8 VA			
Auxiliary circuit	0.0 VA	_	_	
	Yes			
product extension auxiliary switch	res	_	_	
Protective and monitoring functions	01.400.40			
trip class	CLASS 10			
design of the overload release	thermal (bimetallic)			
Short-circuit protection				
product function short circuit protection	Yes			
design of the short-circuit trip	magnetic			
conditional short-circuit current (Iq)	450,000.1			
at 400 V according to IEC 60947-4-1 rated value	150 000 A			
Installation/ mounting/ dimensions				
mounting position	vertical			
fastening method	On adapter for screw and si	nap-on mounting on 35 i	mm standard	
haight	mounting rail 265 mm			
height width	90 mm			
depth	120 mm			
· ·	120 111111			
required spacing  • for grounded parts				
— forwards	32 mm			
— backwards	0 mm			
— upwards	50 mm			
— at the side	10 mm			
— downwards	10 mm			
• for live parts	10 111111			
— forwards	32 mm			
— backwards	0 mm			
— upwards	50 mm			
— downwards	10 mm			
— at the side	10 mm			
Connections/ Terminals				
type of electrical connection				
• for main current circuit	screw-type terminals			
for auxiliary and control circuit	screw-type terminals			
Safety related data	55.51. Typo torrilliaio			
B10 value with high demand rate according to SN 31920	1 000 000			
proportion of dangerous failures	- 1 000 000			
with high demand rate according to SN 31920	73 %			
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front			
Communication/ Protocol				
protocol is supported	No			
<ul><li>PROFINET IO protocol</li><li>PROFIsafe protocol</li></ul>	No			
protocol is supported AS-Interface protocol	No			
Certificates/ approvals	140			
General Product Approval		For use in hazard- ous locations	Declaration of Conformity	



## Confirmation









**Declaration of** Conformity

**Test Certificates** 

Marine / Shipping



Special Test Certific-<u>ate</u>

Type Test Certificates/Test Report







Marine / Shipping







Confirmation

other

Vibration and Shock

Railway

## Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2220-4BB27-0AP0

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2220-4BB27-0AP0

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RA2220-4BB27-0AP0

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3RA2220-4BB27-0AP0&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RA2220-4BB27-0AP0/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2220-4BB27-0AP0&objecttype=14&gridview=view1

last modified:

2/16/2022

