SIEMENS

Data sheet

3RW5225-1AC15



SIRIUS soft starter 200-600 V 63 A, 110-250 V AC Screw terminals Analog output

product brand name	SIRIUS
product category	Hybrid switching devices
product designation	Soft starter
product type designation	3RW52
manufacturer's article number	
 of standard HMI module usable 	<u>3RW5980-0HS00</u>
 of high feature HMI module usable 	<u>3RW5980-0HF00</u>
 of communication module PROFINET standard usable 	<u>3RW5980-0CS00</u>
 of communication module PROFIBUS usable 	<u>3RW5980-0CP00</u>
 of communication module Modbus TCP usable 	<u>3RW5980-0CT00</u>
 of communication module Modbus RTU usable 	<u>3RW5980-0CR00</u>
 of communication module Ethernet/IP 	<u>3RW5980-0CE00</u>
 of circuit breaker usable at 400 V 	3VA2163-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
 of circuit breaker usable at 500 V 	3VA2163-7MN32-0AA0; Type of coordination 1, Iq = 20 kA, CLASS 10
 of circuit breaker usable at 400 V at inside-delta circuit 	<u>3VA2110-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10</u>
 of circuit breaker usable at 500 V at inside-delta circuit 	<u>3VA2110-7MN32-0AA0; Type of coordination 1, Iq = 20 kA, CLASS 10</u>
 of the gG fuse usable up to 690 V 	3NA3830-6; Type of coordination 1. Iq = 65 kA
 of the gG fuse usable at inside-delta circuit up to 500 V 	<u>3NA3830-6; Type of coordination 1, Iq = 65 kA</u>
 of full range R fuse link for semiconductor protection usable up to 690 V 	<u>3NE1022-0: Type of coordination 2. Iq = 65 kA</u>
 of back-up R fuse link for semiconductor protection usable up to 690 V 	<u>3NE8024-1; Type of coordination 2, Iq = 65 kA</u>
General technical data	
starting voltage [%]	30 100 %
stopping voltage [%]	50 %; non-adjustable
start-up ramp time of soft starter	0 20 s
current limiting value [%] adjustable	130 700 %
certificate of suitability	
CE marking	Yes
UL approval	Yes
CSA approval	Yes
product component	
HMI-High Feature	No
 is supported HMI-Standard 	Yes
 is supported HMI-High Feature 	Yes
product feature integrated bypass contact system	Yes
number of controlled phases	3

trin class	CLASS 104 (default) / 10E / 20E: acc. to IEC 60047.4.2
trip class	CLASS 10A (default) / 10E / 20E; acc. to IEC 60947-4-2
 buffering time in the event of power failure for main current circuit 	100 ms
for control circuit	100 ms
	600 V
insulation voltage rated value	
degree of pollution	3, acc. to IEC 60947-4-2
impulse voltage rated value	6 kV 1 800 V
blocking voltage of the thyristor maximum	
service factor	16 kV
surge voltage resistance rated value	O KV
 maximum permissible voltage for safe isolation between main and auxiliary circuit 	600 V
shock resistance	
vibration resistance	15 g / 11 ms, from 12 g / 11 ms with potential contact lifting
	15 mm to 6 Hz; 2g to 500 Hz AC 53a
utilization category according to IEC 60947-4-2 reference code according to IEC 81346-2	
	Q 02/15/2018
Substance Prohibitance (Date)	02/15/2018
product function	Ven
ramp-up (soft starting) ramp down (coff start)	Yes
ramp-down (soft stop)	Yes
Soft Torque	Yes
adjustable current limitation	Yes
pump ramp down intrineig dowing protection	Yes
intrinsic device protection	Yes
motor overload protection	Yes; Electronic motor overload protection
evaluation of thermistor motor protection	No
inside-delta circuit	Yes
auto-RESET	Yes
manual RESET	Yes
remote reset	Yes; By turning off the control supply voltage
communication function	Yes
 operating measured value display 	Yes; Only in conjunction with special accessories
• error logbook	Yes; Only in conjunction with special accessories
• via software parameterizable	No
• via software configurable	Yes
PROFlenergy	Yes; in connection with the PROFINET Standard communication module
• firmware update	Yes
removable terminal for control circuit	Yes
torque control	No
analog output	Yes; 4 20 mA (default) / 0 10 V (parameterizable with High Feature
	HMI)
Power Electronics	
operational current	
 at 40 °C rated value 	63 A
• at 50 °C rated value	56 A
• at 60 °C rated value	51 A
operational current at inside-delta circuit	
• at 40 °C rated value	109 A
• at 50 °C rated value	96 A
• at 60 °C rated value	87.5 A
operating voltage	
rated value	200 600 V
• at inside-delta circuit rated value	200 600 V
relative negative tolerance of the operating voltage	-15 %
relative positive tolerance of the operating voltage	10 %
relative negative tolerance of the operating voltage at inside-delta circuit	-15 %
relative positive tolerance of the operating voltage at inside-delta circuit	10 %
operating power for 3-phase motors	
-F	

• at 230 V at 40 °C rated value	18.5 kW
 at 230 V at 40° C rated value at 230 V at inside-delta circuit at 40 °C rated value 	30 kW
 at 200 V at inside-dena circuit at 40°C rated value at 400 V at 40 °C rated value 	30 kW
 at 400 V at 40 °C rated value at 400 V at inside-delta circuit at 40 °C rated value 	55 kW
 at 500 V at this develop a check at 40°C rated value at 500 V at 40 °C rated value 	37 kW
 at 500 V at 40°C rated value at 500 V at inside-delta circuit at 40 °C rated value 	57 kW
Operating frequency 1 rated value	50 Hz
Operating frequency 2 rated value	60 Hz
relative negative tolerance of the operating frequency	-10 %
relative positive tolerance of the operating frequency	10 %
adjustable motor current	
 at rotary coding switch on switch position 1 	25.5 A
 at rotary coding switch on switch position 2 	28 A
at rotary coding switch on switch position 3	30.5 A
 at rotary coding switch on switch position 4 	33 A
 at rotary coding switch on switch position 5 	35.5 A
 at rotary coding switch on switch position 6 	38 A
 at rotary coding switch on switch position 7 	40.5 A
 at rotary coding switch on switch position 8 	43 A
 at rotary coding switch on switch position 9 	45.5 A
 at rotary coding switch on switch position 10 	48 A
 at rotary coding switch on switch position 11 	50.5 A
 at rotary coding switch on switch position 12 	53 A
 at rotary coding switch on switch position 13 	55.5 A
 at rotary coding switch on switch position 14 	58 A
 at rotary coding switch on switch position 15 	60.5 A
 at rotary coding switch on switch position 16 	63 A
• minimum	25.5 A
adjustable motor current	
• for inside-delta circuit at rotary coding switch on switch position 1	44.2 A
 for inside-delta circuit at rotary coding switch on switch position 2 	48.5 A
 for inside-delta circuit at rotary coding switch on switch position 3 	52.8 A
 for inside-delta circuit at rotary coding switch on switch position 4 	57.2 A
 for inside-delta circuit at rotary coding switch on switch position 5 	61.5 A
 for inside-delta circuit at rotary coding switch on switch position 6 	65.8 A
 for inside-delta circuit at rotary coding switch on switch position 7 	70.1 A
• for inside-delta circuit at rotary coding switch on switch position 8	74.5 A
 for inside-delta circuit at rotary coding switch on switch position 9 	78.8 A
 for inside-delta circuit at rotary coding switch on switch position 10 	83.1 A
 for inside-delta circuit at rotary coding switch on switch position 11 	87.5 A
 for inside-delta circuit at rotary coding switch on switch position 12 	91.8 A
• for inside-delta circuit at rotary coding switch on switch position 13	96.1 A
 for inside-delta circuit at rotary coding switch on switch position 14 	100 A
 for inside-delta circuit at rotary coding switch on switch position 15 	105 A
 for inside-delta circuit at rotary coding switch on switch position 16 	109 A
at inside-delta circuit minimum	44.2 A
minimum load [%]	15 %; Relative to smallest settable le
power loss [W] for rated value of the current at AC	

	0.111
• at 40 °C after startup	31 W
• at 50 °C after startup	29 W
• at 60 °C after startup	27 W
power loss [W] at AC at current limitation 350 %	992 M/
at 40 °C during startup	882 W 744 W
 at 50 °C during startup at 60 °C during startup 	744 W 659 W
Control circuit/ Control	
type of voltage of the control supply voltage	AC
control supply voltage at AC	
• at 50 Hz	110 250 V
• at 60 Hz	110 250 V
relative negative tolerance of the control supply	-15 %
voltage at AC at 50 Hz	
relative positive tolerance of the control supply voltage at AC at 50 Hz	10 %
relative negative tolerance of the control supply voltage at AC at 60 Hz	-15 %
relative positive tolerance of the control supply voltage at AC at 60 Hz	10 %
control supply voltage frequency	50 60 Hz
relative negative tolerance of the control supply voltage frequency	-10 %
relative positive tolerance of the control supply voltage frequency	10 %
control supply current in standby mode rated value	30 mA
holding current in bypass operation rated value	75 mA
locked-rotor current at close of bypass contact maximum	2.5 A
inrush current peak at application of control supply voltage maximum	12.2 A
duration of inrush current peak at application of control supply voltage	2.2 ms
design of the overvoltage protection	Varistor
design of short-circuit protection for control circuit	4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply
Inputs/ Outputs	
number of digital inputs	1
number of digital outputs	3
not parameterizable	2
digital output version	2 normally-open contacts (NO) / 1 changeover contact (CO)
number of analog outputs	1
switching capacity current of the relay outputs	
• at AC-15 at 250 V rated value	3 A
• at DC-13 at 24 V rated value	1 A
Installation/ mounting/ dimensions	
mounting position	+/- 10° rotation possible and can be tilted forward or backward on vertical mounting surface
fastening method	screw fixing
height	306 mm
width	185 mm
depth	203 mm
required spacing with side-by-side mounting • forwards	10 mm
borwards backwards	0 mm
backwards upwards	100 mm
downwards	75 mm
at the side	5 mm
weight without packaging	5.6 kg
Connections/ Terminals	
type of electrical connection	
JES C. C.C.C. Commonien	

 for main current circuit 	box terminal
for control circuit	screw-type terminals
width of connection bar maximum	25 mm
type of connectable conductor cross-sections	
 for main contacts for box terminal using the front clamping point solid 	1x (2.5 16 mm²)
 for main contacts for box terminal using the front clamping point finely stranded with core end processing 	1x (2.5 50 mm²)
 for main contacts for box terminal using the front clamping point stranded 	1x (10 70 mm²)
 at AWG cables for main contacts for box terminal using the front clamping point 	1x (10 2/0)
 for main contacts for box terminal using the back clamping point solid 	1x (2.5 16 mm²)
 at AWG cables for main contacts for box terminal using the back clamping point 	1x (10 2/0)
 for main contacts for box terminal using both clamping points solid 	2x (2.5 16 mm²)
 for main contacts for box terminal using both clamping points finely stranded with core end processing 	2x (2.5 35 mm²)
 for main contacts for box terminal using both clamping points stranded 	2x (6 16 mm²), 2x (10 50 mm²)
 for main contacts for box terminal using the back clamping point finely stranded with core end processing 	1x (2.5 50 mm²)
 for main contacts for box terminal using the back clamping point stranded 	1x (10 70 mm²)
type of connectable conductor cross-sections	
for control circuit solid	1x (0.5 4.0 mm ²), 2x (0.5 2.5 mm ²)
for control circuit finely stranded with core end processing	1x (0.5 2.5 mm²), 2x (0.5 1.5 mm²)
at AWG cables for control circuit solid	1x (20 12), 2x (20 14)
 wire length between soft starter and motor maximum 	800 m
 at the digital inputs at AC maximum 	100 m
tightening torque	
 for main contacts with screw-type terminals 	4.5 6 N·m
 for auxiliary and control contacts with screw-type 	0.8 1.2 N·m
terminals	
tightening torque [lbf·in]	
 for main contacts with screw-type terminals 	40 53 lbf·in
 for auxiliary and control contacts with screw-type terminals 	7 10.3 lbf·in
Ambient conditions	
installation altitude at height above sea level maximum	5 000 m; Derating as of 1000 m, see catalog
ambient temperature	
during operation	-25 +60 °C; Please observe derating at temperatures of 40 °C or above
 during storage and transport 	-40 +80 °C
environmental category	
 during operation according to IEC 60721 	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
during storage according to IEC 60721	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4
during transport according to IEC 60721	2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)
EMC emitted interference	acc. to IEC 60947-4-2: Class A
Communication/ Protocol	
communication module is supported	
PROFINET standard	Yes
EtherNet/IP	Yes
Modbus RTU Modbus TCP	Yes
Modbus TCP PPOEIRUS	Yes
PROFIBUS	Yes

JL/CSA ratings	
manufacturer's article number	
 of circuit breaker 	
 — usable for Standard Faults at 460/480 V according to UL 	Siemens type: 3RV2742, max. 70 A or 3VA51, max. 125 A; lq = 10 kA
 — usable for High Faults at 460/480 V according to UL 	Siemens type: 3VA51, max. 125 A; lq max = 65 kA
 — usable for Standard Faults at 460/480 V at inside-delta circuit according to UL 	Siemens type: 3VA51, max. 125 A; Iq = 10 kA
 — usable for High Faults at 460/480 V at inside- delta circuit according to UL 	Siemens type: 3VA51, max. 125 A; lq max = 65 kA
 — usable for Standard Faults at 575/600 V according to UL 	Siemens type: 3RV2742, max. 70 A or 3VA51, max. 125 A; lq = 10 kA
— usable for Standard Faults at 575/600 V at inside-delta circuit according to UL	Siemens type: 3VA51, max. 125 A; Iq = 10 kA
 of the fuse usable for Standard Faults up to 575/600 V according to UL 	Type: Class RK5 / K5, max. 200 A; lq = 10 kA
— usable for High Faults up to 575/600 V according to UL	Type: Class J / L, max. 225 A; lq = 100 kA
— usable for Standard Faults at inside-delta circuit up to 575/600 V according to UL	Type: Class RK5 / K5, max. 200 A; lq = 10 kA
— usable for High Faults at inside-delta circuit up to 575/600 V according to UL	Type: Class J / L, max. 225 A; lq = 100 kA
operating power [hp] for 3-phase motors	
at 200/208 V at 50 °C rated value	15 hp
• at 220/230 V at 50 °C rated value	20 hp
• at 460/480 V at 50 °C rated value	40 hp
• at 575/600 V at 50 °C rated value	50 hp
at 200/208 V at inside-delta circuit at 50 °C rated value	30 hp
 at 220/230 V at inside-delta circuit at 50 °C rated value 	30 hp
 at 460/480 V at inside-delta circuit at 50 °C rated value 	75 hp
 at 575/600 V at inside-delta circuit at 50 °C rated value 	75 hp
contact rating of auxiliary contacts according to UL	R300-B300
afety related data	
protection class IP on the front according to IEC 60529	IP00; IP20 with cover
touch protection on the front according to IEC 60529 electromagnetic compatibility	finger-safe, for vertical contact from the front with cover in accordance with IEC 60947-4-2
ertificates/ approvals	
General Product Approval	EMC
Confirmation	
CSA CCC	UL BEERE RCM
Declaration of Conformity Test Certification	ates Marine / Shipping
UK (f Type Test Ce ates/Test Re	
EG-Konf.	ABS BUREAU LRS
	VENTIAS
Marine / Shipping other	
ina no / onipping Ouler	



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5225-1AC15

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5225-1AC15

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RW5225-1AC15

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RW5225-1AC15&lang=en


Characteristic: Tripping characteristics, I²t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RW5225-1AC15/char

Characteristic: Installation altitude

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RW5225-1AC15&objecttype=14&gridview=view1 Simulation Tool for Soft Starters (STS)

https://support.industry.siemens.com/cs/ww/en/view/101494917



last modified:

4/10/2022 🖸