т <u>Ω</u> т	т (0	σ	Þ	
			LAYOUT SHOWN AS	EXAMPLE		
Keying Shown as ex	ample					
CHARACTERISTICS	Connector dimension					
-Standard : Based on MIL-DTL-38999 Series III	DimNominalØS44.9 Max					-
-Shell Material : Aluminium -Shell Plating : Olive drab Cadmium	Z 31 Max V THREAD M34x1-6g	SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with				
-Insulator : Thermoplastic	V THILAD WISHAT-Og		the Specifications issued by either	of the Parties or by a th		
-Contacts : Copper Alloy			(professional recommend	ation, technical notice.)		
-Seals & Grommet : Silicon Elastomer			Cour		& Control List	
-Contact Plating : Gold over copper Alloy 0.8µm minimum			FR	Not	Listed	
-Durability : 500 Mating cycles -Delivered with Souriau contacts and Accessories		PN: 8D523W06BA				
-Temperature Range -65°C to +175°C	г		1			
-Salt Spray : 500 hours		A 07-10-2016	First Release			
_		ISS DATE	Latest modification - by			IOD N°
		Designed By:	Date:	CUS	TOMER DRAWING	
		TITLE	TITLE Aluminium Plug 8D series			
BASIC SERIES: 8D 5 - 23 W 06 B A SHELL TYPE : Plug with RFI Shielding - - 23 W 06 B A		SCALE . NA	General linear Tolerances:	N	PRDS / PROJECT 859	
CONTACT TYPE : Standard Crimp Contact	ORIENTATION : A				This document is the property o SOURIAU	of
SHELL SIZE : 23	CONTACT TYPE : SOCKET(500 Matings)	SOURIAU	WWW.SOURIAU.		it must not be reproduced or ommunicated without permissio	
PLATING : W = Olive drab Cadmium	CONTACT TYPE : SOCKET(SOU Matings)	FORMAT		J DRG N°		SHEET
	CONTACT LATOUT . 25-00	A3	8D523V			1/2

ſ	т	۵	п	т	D	0
		Contact Layout				
		06				
4						
		6#8 Concentric				
		Twinax Service M				
		23-06]			
	Ctc	X Y	_			
	A	0 9.24	-			
	B	8.81 2.87 5.43 -7.49	-			
ယ	D	-5.43 -7.49				
	E	-8.81 2.87	-			
	F	0 0				
	1					
						SOURIAU shall not be liable for an due to a use of the Products wi the Specifications issued by either o (professional recommenda
N						Count FR
						PN: 8D523\
					A 07-10-20	16 First Release
					ISS DATE	
					Designed By:	Date:
					TITLE	Alumir
_					SCALE NA	General linear Tolerances: ±
					SOURIA	U WWW.SOURIAU.C
					FORMAT	SOURIAU
					A3	8D523W
l	Н	G	F	E	D	C

