

DESCRIPTION: 35° ENTRY - DIE CAST





DIMENSIONS (IN.)					
No. OF PINS	Α	В	С	D	E
09	1.693	0.610	0.984	1.260	0.512
	43.00	15.50	24.99	32.00	13.00
15	1.693	0.610	1.312	1.591	0.512
	43.00	15.50	33.32	40.40	13.00
25	1.890	0.610	1.852	2.126	0.512
	48.00	15.50	47.04	54.00	13.00
37	2.087	0.610	2.500	2.776	0.512
	53.00	15.50	63.50	70.50	13.00

SPECIFICATION:

MATERIAL: ZINC, NICKEL PLATED,

COPPER UNDER PLATE

OPERATING TEMPERATURE: -40°C TO +120°C

BACKSHELL KIT INCLUDES:

(2) BACKSHELL HALVES

(2) STRAIN RELIEF CLAMPS

(2) STRAIN RELIEF SCREWS

(2) MOUNTING SCREWS

(2) THUMBSCREWS ***(SEE NOTE)***

(3-SETS) METALIZED PLASTIC INSERTS

NOTE:

9-POSITION - 1 LONG THUMBSCREW WITH PLASTIC CAP 15-POSITION - 1 LONG THUMBSCREW WITH PLASTIC CAP 1 SHORT THUMBSCREW WITH METAL CAP 25-POSITION - 1 LONG THUMBSCREW WITH PLASTIC CAP

1 SHORT THUMBSCREW WITH PLASTIC CAP 37-POSITION - 1 LONG THUMBSCREW WITH PLASTIC CAP 1 SHORT THUMBSCREW WITH PLASTIC CAP

953-YYY-030R121 **SERIES** POSITIONS 009 015 025 037 MATERIAL 030 = DIE CAST (NICKEL) RoHS COMPLIANT R = HIGH TEMP. PROCESS COLOR -12 = NICKEL OVER COPPER **PUT-UP** 1 = KIT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION

> SCALE: 1:1

DRAWN:

C. SMITH

CHECKED:

DATE:

03-26-07

REV

2

DATE:

NorComp

DWG NO. 953-YYY-030R121

SHEET

ROHS COMPLIANT