


Data sheet for SINAMICS G120X

Article No.: 6SL3220-1YE54-0CP0

Client order no. : Order no. : Offer no. : Remarks :



Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
0.90 0.95		
0.99		
0.98		
74 dB		
6.170 kW		
RFI suppression filter for Category C3		
Category C3		
without		

Communication

Communication PROFIBUS DP



Item no. : Consignment no. : Project :

Inputs / outputs		
Standard digital inputs		
Number	6	
Switching level: 0 → 1	11 V	
Switching level: $1 \rightarrow 0$	5 V	
Max. inrush current	15 mA	
Fail-safe digital inputs		
Number	1	
Digital outputs		
Number as relay changeover contact	2	
Output (resistive load)	DC 30 V, 5.0 A	
Number as transistor	0	
Analog / digital inputs		
Number	2 (Differential input)	
Resolution	10 bit	
Switching threshold as digital input		
0 → 1	4 V	
1 → 0	1.6 V	
Analog outputs		
Number	1 (Non-isolated output)	

PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5\,^{\circ}\text{C}$

Closed-loop control techniques		
V/f linear / square-law / parameterizable	Yes	
V/f with flux current control (FCC)	Yes	
V/f ECO linear / square-law	Yes	
Sensorless vector control	Yes	
Vector control, with sensor	No	
Encoderless torque control	No	
Torque control, with encoder	No	




Data sheet for SINAMICS G120X

Article No.: 6SL3220-1YE54-0CP0

Amhi	ent conditions	
Amble		
Standard board coating type	Class 3C2, according to IEC 60721-3-3: 2002	
Cooling	Air cooling using an integrated fan	
Cooling air requirement	0.210 m ³ /s (7.416 ft ³ /s)	
Installation altitude	1,000 m (3,280.84 ft)	
Ambient temperature		
Operation	-20 45 °C (-4 113 °F)	
Transport	-40 70 °C (-40 158 °F)	
Storage	-25 55 °C (-13 131 °F)	
Relative humidity		
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible	
Connections		
Signal cable		
Conductor cross-section	0.15 1.50 mm ² (AWG 24 AWG 16)	
Line side		
Version	M10 screw	
Conductor cross-section	35.00 2 x 185.00 mm ² (AWG 1 MCM 2 x 350)	
Motor end		
Version	M10 screw	
Conductor cross-section	35.00 2 x 185.00 mm ² (AWG 1 MCM 2 x 350)	
DC link (for braking resistor)		
PE connection	M10 screw	
Max. motor cable length		
Shielded	200 m (656.17 ft)	

Machanical data		
Mechanical data		
IP20 / UL open type		
FSG		
120 kg (264.56 lb)		
305 mm (12.01 in)		
999 mm (39.33 in)		
369 mm (14.53 in)		
Standards		
UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH		
EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC		

Converter losses to IEC61800-9-2*		
Efficiency class	IE2	
Comparison with the reference converter (90% / 100%)	45.7 %	



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

 $^{^{1)}}$ The output current and HP ratings are valid for the voltage range 440V-480V

³⁾Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.