

## MLFB-Ordering data

#### 6SL3220-3YE60-0CB0



Client order no. : Order no. : Offer no. :

Remarks:

Item no. : Consignment no. :

Project :

Rated data			General tech. specifications	
nput			Power factor λ	0.75 0.93
Number of phases	3 AC		Offset factor cos φ	0.96
Line voltage	380 480 V +10 % -10 %		Efficiency η	0.98
Line frequency	47 63 Hz		Sound pressure level (1m)	74 dB
Rated voltage	400V IEC	480V NEC	Power loss	8.385 kW
Rated current (LO)	750.00 A	602.00 A		RFI suppression filter for Category C3
Rated current (HO)	562.00 A	461.00 A	Filter class (integrated)	
utput			EMC category (with accessories)	Category C3
Number of phases	3 AC			3 7
Rated voltage	400V IEC	480V NEC	Ambient conditions	
Rated power (LO)	400.00 kW	500.00 hp	Standard board coating type	Class 3C2, according to IEC 607 3: 2002
Rated power (HO)	315.00 kW	350.00 hp		
Rated current (LO)	720.00 A	590.00 A	Cooling	Air cooling using an integrated
Rated current (HO)	640.00 A	452.00 A		
Rated current (IN)	735.00 A		Cooling air requirement	0.362 m³/s (12.784 ft³/s)
Max. output current	972.00 A		Installation altitude	1000 m (3280.84 ft)
Pulse frequency	4 kHz		Ambient temperature	
Output frequency for vector control	0 100 Hz		Operation	0 45 °C (32 113 °F)
			Transport	-40 70 °C (-40 158 °F)
Output frequency for V/f control	0 100 Hz		Storage	-25 55 °C (-13 131 °F)
			Relative humidity	
			Max. operation	95 % At 40 °C (104 °F), conden and icing not permissible

#### Overload capability

#### Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

#### High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time



#### **MLFB-Ordering data**

6SL3220-3YE60-0CB0



Machanical	data	Closed lean	Figure		
Mechanical data		Closed-loop o	Closed-loop control techniques		
Degree of protection	IP20 / UL open type	V/f linear / square-law / parame	e <b>terizable</b> Yes		
Size	FSH				
Net weight	159 kg (350.54 lb)	V/f with flux current control (FC	CC) Yes		
Width	548 mm (21.57 in)	V/f ECO linear / square-law	Yes		
Height	1695 mm (66.73 in)	Sensorless vector control	Yes		
Depth	393 mm (15.47 in)	Vector control, with sensor	No		
Inputs / ou		Encoderless torque control	Yes		
tandard digital inputs		Torque control, with encoder	No		
Number	6				
Switching level: 0→1	11 V	Communication			
-	5 V	Communication	USS, Modbus RTU, BACnet MS/TF		
Switching level: 1→0		Connections			
Max. inrush current	15 mA	Signal cable			
ail-safe digital inputs		Conductor cross-section	0.15 1.50 mm²		
Number	1		(AWG 24 AWG 16)		
igital outputs		Line side			
Number as relay changeover contact	2	Version	M12 screw		
Output (resistive load)	DC 30 V, 5.0 A	Conductor cross-section	240.00 mm <sup>2</sup> (MCM 2 x 500 MCM 4 x 500)		
Number as transistor	0	Motor end			
nalog / digital inputs		Version	M12 screw		
Number	2 (Differential input)	Conductor cross-section	240.00 mm <sup>2</sup> (MCM 2 x 500 MCM 4 x 500)		
Resolution	10 bit	DC link (for braking resistor)			
witching threshold as digital in	put	PE connection	M12 screw		
0→1	4 V	Max. motor cable length			
1→0	1.6 V	Shielded	150 m (492.13 ft)		
nalog outputs		Silielueu	130 III (+32.13 IL)		
	4 (3)				
Number	1 (Non-isolated output)				

### PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected: PTC, KTY and Thermo-Click, accuracy  $\pm 5~^{\circ}\text{C}$ 



#### **MLFB-Ordering data**

#### 6SL3220-3YE60-0CB0



Converter losses to EN 50598-2*		Standards		
Efficiency class		IE2	Compliance with standards	UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH
Comparison with the reference converter (90% / 100%)		-40.40 %		
6371.0 W (1.25 %)	7235.0 W (1.42 %)	8395.0 W (1.65 %)	CE marking	EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC
3029.0 W (0.59 %)	3376.0 W (0.66 %)	3799.0 W (0.75 %)		

90%

 $\label{thm:converter:thm:con$ 

50%

2154 W (0.42 %)

The diagram shows the losses for the points (as per standard EN 50598) of the relative torque generating current (I) over the relative motor stator frequency(f). The values are valid for the basic version of the converter without options/components.

1997.0 W (0.39 %)

# Operator panel: Intelligent Operator Panel (IOP-2)

Screen		Ambient conditions	
Display design	LCD colors	Ambient temperature during	
	220 240 8'	Operation	0 50 °C (32 122 °F)
Screen resolution	320 x 240 Pixel		55 °C only with door mounting kit
Mechanical data		Storage	-40 70 °C (-40 158 °F)
Degree of protection	IP55 / UL type 12	Transport	-40 70 °C (-40 158 °F)
Net weight	0.13 kg (0.30 lb)	Relative humidity at 25°C du	uring
Width	70.0 mm (2.76 in)	Max. operation	95 %
Height	106.85 mm (4.21 in)		
Depth	19.65 mm (0.77 in)	Approvals	
	15.05 11111 (0.77 111)	Certificate of suitability	CE, cULus, EAC, KCC, RCM

<sup>\*</sup>converted values