## **Panasonic**

## AQS221FR2S | PhotoMOS RF SOP 4 Form A CxR10 Voltage-sensitive



**Product Number** AQS221FR2S Part Number AQS221FR2S Surface-mount terminal, Tube packing style, Load Details voltage:40 V PhotoMOS RF SOP 4 Form A CxR10 Voltage-Product name Features Space-saving 4-channel type Built-in input resistor



## **Spec Detail**

Part Number

As of November 19, 2019

Specifications and design of the products are subject to change without notice for the product improvement.

Item	Specifications
------	----------------

AQS221FR2S

Product Number AQS221FR2S

Features Low on resistance (R type)

RF SOP 4 Form A CxR10 Voltage-sensitive Product name

Туре RF

Package SOP16

Voltage type AC/DC

Input voltage [ V<sub>IN</sub> ] 6 V

Input reverse voltage [ V<sub>RIN</sub> ]

Power dissipation [Pin] 260 mW

Load voltage [ V<sub>L</sub> ] 40 V

Load current 0.16 A

Continuous load current [ I<sub>L</sub> ] 0.16 A

Peak load current [ Ipeak ] 0.2 A

600 mW Power dissipation [Pout]

Total power dissipation [ P<sub>t</sub> ] 650 mW

I/O isolation voltage [ V<sub>iso</sub> ] 500 Vrms

Ambient temperature: Operating [

-40 to +85°C -40 to +185°F

Ambient temperature: Storage [ T<sub>stg</sub> ] -40 to +100°C -40 to +212°F

Operate voltage (Typical) [  $V_{Fon}$  ] 1.3 V Operate voltage (Maximum) [ V<sub>Fon</sub> ]

Turn off voltage (Minimum) [ V<sub>Foff</sub> ] 0.8 V

Turn off voltage (Typical) [ V<sub>Foff</sub> ] 1.3 V

Input current (Typical) [ I<sub>IN</sub> ] 8.5 mA

On resistance (Typical) [ R<sub>on</sub> ] 0.75 ohm

ON resistance (Maximum) [ R<sub>on</sub> ] 1.25 ohm

Output capacitance (Typical) [  $C_{out}$  ] 12.5 pF

Output capacitance (Maximum) [ Cout 18 pF

Off state leakage current (Typical) [

I<sub>Leak</sub>]

0.02 nA

Off state leakage current (Maximum) [

I<sub>Leak</sub>]

10 nA

Over current protection Nothing

0.07 ms Turn on time (Typical)

Turn on time (Maximum) 0.5 ms

0.07 ms Turn off time (Typical)

Turn off time (Maximum) 0.2 ms

I/O capacitance (Typical) [ C<sub>iso</sub> ] 0.8 pF

I/O capacitance (Maximum) [ C<sub>iso</sub> ] 1.5 pF

Initial I/O isolation resistance

(Minimum) [ R<sub>iso</sub> ]

1,000 M ohm

[Recommended operating conditions]

Input voltage [ V<sub>IN</sub> ]

Min.: 4.5 V, Max.: 5.5 V

Surface-mount terminal

[Recommended operating conditions]

Load voltage [ V<sub>L</sub> ]

Max.: 15 V

[Recommended operating conditions]

Continuous load current [ I<sub>L</sub> ]


Max.: 0.16 A

Terminal shape

Contact arrangement 4 Form A

Packing style Tube packing style


External dimensions



Terminal thickness = 0.15 .006 General tolerance: ±0.1 ±.004 mm inch

## Recommended mounting pad (Top view)

Recommended mounting pad (Top view)



Tolerance: ±0.1 ±.004 mm inch

© Panasonic Corporation