

Description: 1005 5GNR-n79 Band Pass Filter

PART NUMBER: BPF1005LRPQR4700L

Features:

Compact size: 1.0x0.5x0.32mm

· RoHS compliant

Applications:

WWAN

5GNR

ELECTRICAL SPECIFICATIONS

DESCRIPTION	Value		
Pass Band	4400~5000 MHz		
Insertion Loss	1.74 (typ.) 2.5 dB max.		
Return Loss	17.5 (typ.) 14 dB (Min.)		
Attenuation	42.2dB Typ./ 30dB Min.@ 600~960 MHz 38.5dB Typ./ 33dB Min.@ 1164~1300 MHz 39.9dB Typ./ 30dB Min.@ 1476~1511 MHz 39.6dB Typ./ 30dB Min.@ 1559~1610 MHz 39.9dB Typ./ 30dB Min.@ 1805~2200 MHz 51.4dB Typ./ 37dB Min.@ 2300~2690 MHz 35.2dB Typ./ 25dB Min.@ 3055~3490 MHz 29.6dB Typ./ 15dB Min.@ 3490~3600 MHz -dB Typ./ 3 dB Min.@ 5490~5670 MHz 3 dB Typ./ 6 dB Min.@ 5670~5875 MHz 13.8dB Typ./ 7 dB Min.@ 5875~6100 MHz 22.5dB Typ./ 15dB Min.@ 6100~6980 MHz 39.1dB Typ./ 25dB Min.@ 8800~10000 MHz 22.4dB Typ./ 15dB Min.@ ref 13200~15000 MHz		
Operating Temperature	-40 ~ +85°C		

In the effort to improve our products, we reserve the right to make changes judged to be necessary. $\texttt{CONFIDENTIAL} \ \texttt{AND} \ \texttt{PROPRIETARY} \ \texttt{INFORMATION}$

ROHS

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:




Description: 1005 5GNR-n79 Band Pass Filter

PART NUMBER: BPF1005LRPQR4700L

MECHANICAL DIMENSION

Outline




Termination

Terminal name	Function
P1	Input
P2	GND
P3	Output
P4	NC
P5	GND
P6	NC
(6) (5)	(4)
(1) (2)	(3)
	-

Mechanical

	Dimension
L (mm)	1.00±0.05
W (mm)	0.50 ± 0.05
T (mm)	0.32(Max.)
a (mm)	0.18 ± 0.05
b (mm)	0.125 ± 0.05
c (mm)	0.18 ± 0.05
d (mm)	0.15 ± 0.05
e (mm)	0.36 ± 0.05
D1-D2	0 ± 0.04
D3-D4	0 ± 0.04

Reference design of EVB



Unit: mm


Line width should be designed to match 50Ω characteristic impedance, depending on PCB material and thickness.



Description: 1005 5GNR-n79 Band Pass Filter


PART NUMBER: BPF1005LRPQR4700L

MEASURING DIAGRAM



Test Instrument : Agilent E5071A Network Analyzer.

ELECTRICAL PERFORMANCES



 Measured on Agilent E5071C Network Analyzer

Frequency Characteristics





Description: 1005 5GNR-n79 Band Pass Filter

PART NUMBER: BPF1005LRPQR4700L

RE\	/ISI	ON	HIS	TORY
-----	------	----	-----	------

RevisionDateDescriptionVersion 1Dec. 29, 2021- New issue

