






SMA ATTENUATOR 30 DB 18 GHZ 2W

PAGE 1/2 ISSUE 19-02-16B SERIES ATTENUATOR PART NUMBER R411830121





SCALE 1:1



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body Male center contact	STAINLESS STEEL BERYLLIUM COPPER	PASSIVATED GOLD 2 OVER NICKEL 2
Female center contact	BERYLLIUM COPPER	GOLD 1.3 OVER NICKEL2
Outer contact	-	-
Insulator	PTFE	
Gasket	SILICONE RUBBER	
Substrate	ALUMINA	
Resistor	THIN FILM	
Others parts	-	-





SMA ATTENUATOR 30 DB 18 GHZ 2W

PAGE 2/2	ISSUE 19-02-16B	SERIES ATTENUATOR	PART NUMBER R411830121
-----------------	------------------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 4	4 - 8	8 - 12.4	12.4 - 18
V.S.W.R (≤)	1.15	1.20	1.25	1.35
Deviation(±dB)	1	1	1	1.2

Operating Frequency Range	DC - 18	GHz
Impedance	50	Ω
Nominal Attenuation	30	dB
Peak power at 25°C (1µs, 1‰)	100	W
Average power at 25°C	2	W (Free Air Cooled)
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	SMA	Male Female	MIL-C 39012
Weight	8,2800 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55 /+125	°C
Storage temperature range	-55 /+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS