SIEMENS

Data sheet US2:73QT34DFA



Enclosed soft starter, Controller 3RW44536BC34, Std. duty rating 400Hp @460V, Std. duty current rating 494A, Control voltage 115 AC, Noncombination type, Enclosure type 3/3R, Weather proof outdoor use

Figure similar

product brand name	Class 73
design of the product	Enclosed soft starter
special product feature	Control transformer, built-in overload relay and bypass contactor included.
General technical data	
weight [lb]	412 lb
Height x Width x Depth [in]	90 × 40 × 20 in
touch protection against electrical shock	NA for enclosed products
installation altitude [ft] at height above sea level maximum	6560 ft
ambient temperature [°F]	
during storage	-22 +149 °F
during operation	-4 +104 °F
ambient temperature	
during storage	-30 +65 °C
during operation	-20 +40 °C
country of origin	USA
Power and control electronics	
manufacturer's article number of soft starter	3RW44536BC34
number of poles for main current circuit	3
design of power semiconductors (thyristors) for soft starter control	3 controlled phases
operating range factor supply voltage rated value	0.85 1.1
operating range factor of control voltage rated value	0.85 1.1
operating condition for standard duty	Class 10 standard duty (350% of motor FLA for 10 seconds)
operating condition for severe duty	Class 20 severe duty (350% of motor FLA for 20 seconds)
Features and functions	
ramp-up (soft starting)/ramp-down (soft stop)	Yes
starting voltage [%]	20 100 %
stopping voltage [%]	20 100 %
voltage ramp	Yes
ramp-up time	1 360 s
ramp-down time	1 360 s
torque control	Yes
starting torque [%]	20 100 %
stopping torque [%]	20 100 %
torque limitation [%]	20 200 %
ramp time of torque	1 360 s
adjustable current limitation	Yes
creep speed in both directions of rotation	Yes

	Vac
pump ramp down	Yes
integrated bypass contact system	Yes
external isolation contactor	No
intrinsic device protection	Yes
overload protection	Yes
trip class	CLASS 5 / 10 / 15 / 20 / 30
reset function	Manual and automatic
thermistor motor protection	Yes
inside-delta circuit	Yes
breakaway pulse	Yes
DC braking	Yes
combined braking	Yes
motor heating	Yes
configuration of control input 1	Factory set as START MOTOR
configuration of control input 2	programmable
configuration of control input 3	programmable
configuration of control input 4	Factory set as TRIP RESET
configuration of relay output 1	Factory set as ON-TIME MOTOR
configuration of relay output 2	programmable
configuration of relay output 3	programmable
configuration of relay output 4	Factory set as GROUP ERROR
display version	Graphic display
operating measured value display	Yes
product extension optional human machine interface module	Yes
type of communication optional	With optional Profibus or Profinet
error logbook	Yes
event list	Yes
slave pointer function	Yes
trace function	Yes
number of parameter sets	3
engineering software (Soft Starter ES)	Yes
	100
disconnector functionality	No
disconnector functionality	No
Contactor	
Contactor size of contactor	No NA
Contactor size of contactor Coil	NA
Contactor size of contactor Coil type of voltage of the control supply voltage	
Contactor size of contactor Coil type of voltage of the control supply voltage control supply voltage	NA AC
contactor size of contactor Coil type of voltage of the control supply voltage control supply voltage • at AC at 50 Hz rated value	NA AC 115 V
Contactor size of contactor Coil type of voltage of the control supply voltage control supply voltage	NA AC
contactor size of contactor Coil type of voltage of the control supply voltage control supply voltage • at AC at 50 Hz rated value	NA AC 115 V
Contactor size of contactor Coil type of voltage of the control supply voltage control supply voltage • at AC at 50 Hz rated value • at AC at 60 Hz rated value	NA AC 115 V
contactor size of contactor Coil type of voltage of the control supply voltage control supply voltage • at AC at 50 Hz rated value • at AC at 60 Hz rated value Enclosure	NA AC 115 V 115 V
contactor size of contactor Coil type of voltage of the control supply voltage control supply voltage • at AC at 50 Hz rated value • at AC at 60 Hz rated value Enclosure degree of protection NEMA rating	NA AC 115 V 115 V 3, 3R
contactor size of contactor Coil type of voltage of the control supply voltage control supply voltage • at AC at 50 Hz rated value • at AC at 60 Hz rated value Enclosure degree of protection NEMA rating degree of protection NEMA rating of the enclosure	NA AC 115 V 115 V 115 V NA AC
contactor size of contactor Coil type of voltage of the control supply voltage control supply voltage • at AC at 50 Hz rated value • at AC at 60 Hz rated value Enclosure degree of protection NEMA rating degree of protection NEMA rating of the enclosure design of the housing	NA AC 115 V 115 V 3, 3R NEMA 3/3R Weather proof for outdoor use
contactor size of contactor Coil type of voltage of the control supply voltage control supply voltage	NA AC 115 V 115 V 3, 3R NEMA 3/3R Weather proof for outdoor use
contactor size of contactor Coil type of voltage of the control supply voltage control supply voltage	NA AC 115 V 115 V 115 V Weather proof for outdoor use Fan
contactor size of contactor Coil type of voltage of the control supply voltage control supply voltage	NA AC 115 V 115 V 115 V Weather proof for outdoor use Fan Vertical
contactor size of contactor Coil type of voltage of the control supply voltage control supply voltage • at AC at 50 Hz rated value • at AC at 60 Hz rated value Enclosure degree of protection NEMA rating degree of protection NEMA rating of the enclosure design of the housing type of cooling Mounting/wiring mounting position fastening method wire length between motor starter and motor maximum	NA AC 115 V 115 V 115 V Weather proof for outdoor use Fan Vertical Surface mounting and installation
contactor size of contactor Coil type of voltage of the control supply voltage control supply voltage	NA AC 115 V 115 V 115 V 3, 3R NEMA 3/3R Weather proof for outdoor use Fan Vertical Surface mounting and installation 500 m
contactor size of contactor Coil type of voltage of the control supply voltage control supply voltage	NA AC 115 V 115 V 115 V 3, 3R NEMA 3/3R Weather proof for outdoor use Fan Vertical Surface mounting and installation 500 m Box lug
contactor size of contactor Coil type of voltage of the control supply voltage control supply voltage	NA AC 115 V 115 V 115 V 3, 3R NEMA 3/3R Weather proof for outdoor use Fan Vertical Surface mounting and installation 500 m Box lug 2x (600 kcmil 2 AWG) 75 °C
size of contactor Coil type of voltage of the control supply voltage control supply voltage at AC at 50 Hz rated value at AC at 60 Hz rated value Enclosure degree of protection NEMA rating degree of protection NEMA rating of the enclosure design of the housing type of cooling Mounting/wiring mounting position fastening method wire length between motor starter and motor maximum type of electrical connection for supply voltage line-side at AWG cables single or multi-stranded temperature of the conductor for supply material of the conductor for supply	NA AC 115 V 115 V 3, 3R NEMA 3/3R Weather proof for outdoor use Fan Vertical Surface mounting and installation 500 m Box lug 2x (600 kcmil 2 AWG) 75 °C CU
contactor size of contactor Coil type of voltage of the control supply voltage control supply voltage	NA AC 115 V 115 V 115 V 3, 3R NEMA 3/3R Weather proof for outdoor use Fan Vertical Surface mounting and installation 500 m Box lug 2x (600 kcmil 2 AWG) 75 °C
size of contactor Coil type of voltage of the control supply voltage control supply voltage	NA AC 115 V 115 V 115 V 3, 3R NEMA 3/3R Weather proof for outdoor use Fan Vertical Surface mounting and installation 500 m Box lug 2x (600 kcmil 2 AWG) 75 °C CU screw-type terminals
size of contactor Coil type of voltage of the control supply voltage control supply voltage at AC at 50 Hz rated value at AC at 60 Hz rated value Enclosure degree of protection NEMA rating degree of protection NEMA rating of the enclosure design of the housing type of cooling Mounting/wiring mounting position fastening method wire length between motor starter and motor maximum type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded temperature of the conductor for supply maximum permissible material of the conductor for supply type of electrical connection for auxiliary and control circuit tightening torque [lbf-in] for auxiliary and control contacts with screw-type terminals	AC 115 V 115 V 115 V 3, 3R NEMA 3/3R Weather proof for outdoor use Fan Vertical Surface mounting and installation 500 m Box lug 2x (600 kcmil 2 AWG) 75 °C CU screw-type terminals 7 10 lbf·in

Short-circuit current rating	
design of the fuse link for short-circuit protection of the main circuit required	100kA@600V (Class L)
design of the short-circuit trip	Thermal magnetic circuit breaker
breaking capacity maximum short-circuit current (Icu)	
• at 240 V	65 kA
• at 480 V	65 kA
• at 600 V	0 kA
certificate of suitability	NEMA ICS 2; UL 508A
Further information	

Industrial Controls - Product Overview (Catalogs, Brochures,...)

www.usa.siemens.com/iccatalog

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:73QT34DFA

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


https://support.industry.siemens.com/cs/US/en/ps/US2:73QT34DFA


 $Image\ database\ (product\ images,\ 2D\ dimension\ drawings,\ 3D\ models,\ device\ circuit\ diagrams,\ EPLAN\ macros,\ ...)$

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:73QT34DFA&lang=en

Certificates/approvals

https://support.industry.siemens.com/cs/US/en/ps/US2:73QT34DFA/certificate





D69015H11

last modified: 11/30/2021 🖸