


SMD 3.4x3.1 to 7.0x3.0 PACKAGE

PRODUCT FEATURES

- High selectivity, suitable for narrowband communication
- Compact structure and small size
- Electrical performance won't be affected by external electromagnetic interference
- Suitable for matching with different ICs
- Automatic on-line, can be reflowed
- RoHS compliant


PRODUCT PHOTO




PRODUCT SPECIFICATIONS

Part Number	3dB Bandwidth (KHz)	20dB Bandwidth (KHz)Max	Insertion Loss(dB)	Spurious Attenuation (9-12MHz)(dB)min	Input/Output Impedance(Ω)
HCCFA10.7MJ	150 \pm 40	430	10	30	330
HCCFV10.7MJ	150 \pm 40	380	5.5 \pm 2.0	35	330
HCCFA10.7MS3	180 \pm 40	520	7	30	330
HCCFV10.7MS3	180 \pm 40	470	4.0 \pm 2.0	35	330
HCCFA10.7MS2	230 \pm 50	570	6	30	330
HCCFV10.7MS2	230 \pm 50	510	3.5 \pm 2.0	35	330
HCCFA10.7MA5	280 \pm 50	650	6	30	330
HCCFV10.7MA5	280 \pm 50	590	3.0 \pm 2.0	35	330
HCCFV10.7MA20	330 \pm 50	700	3.0 \pm 2.0	30	330
HCCFV10.7MA19	\pm 175min	950	3.0 \pm 2.0	20(5-15MHz)	470
HCCFS10.7MS3	180 \pm 40	470	4.5 \pm 2.0	30	330
HCCFS10.7MS2	230 \pm 50	510	3.5 \pm 2.0	30	330
HCCFS10.7MA5	280 \pm 50	590	3.0 \pm 2.0	30	330
HCCFS10.7MA20	330 \pm 50	700	3.0 \pm 2.0	30	330

PACKAGE OUTLINE / DIMENSIONS



HCCFV/A Series



HCCFS Series