







# Engineer Drawing



1.MATERIAL  
 HOUSING:LCP UL 94V-0  
 ACTUATOR:LCP UL 94V-0  
 CONTACTS:COPPER ALLOY  
 PEG: COPPER ALLOY

2.PLATING:  
 CONTACTS:GOLD FLASH OVER NICKEL  
 PEG:TIN OVER NICKEL

3.PART NO:  
 OPERATING VOLTAGE:50V AC,DC  
 CURRENT RATING:0.5A AC,DC  
 OPERATING TEMPERATURE:-25C~+85C

No. of Contacts	DIM.		
	A	B	C
08	3.50	8.92	4.50
09	4.00	9.42	5.00
10	4.50	9.92	5.50
20	9.50	14.92	10.50
24	11.50	16.92	12.50
25	12.00	17.42	13.00
28	13.50	18.92	14.50
30	14.50	19.92	15.50
40	19.50	24.92	20.50
50	24.50	29.92	25.50
60	29.50	34.92	30.50

**IPFP 05 25 \* \* \* \* \***

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series Type
- ② Pitch
- ③ Height
- ④ Internal Code
- ⑤ Pin Code
- ⑥ Serial Code
- ⑦ Package Code
- ⑧ Other Code

GENERAL TOLERANCE  
 UNLESS OTHERWISE  
 SPECIFIED

X :  $\pm 0.30$   
 X.X :  $\pm 0.25$   
 X.XX :  $\pm 0.15$   
 ANG :  $\pm 2^\circ$



[www.i-ncp.com](http://www.i-ncp.com)

PART NO  
 IPFP0525 XX

DRAWING NO  
 IPFP052507

NAME  
 0.5Pitch 2.5H SMT CONN  
 FPC



SHEET 1 OF 1

UNITS:mm

SCALE:1:1

REV.01