עם ד 			0			
Z'	ØS					
			LAYOUT SHOWN AS EXAMPL	E		
	Keying Shown as example					
CHARACTERISTICS		-				
-Standard : Based on MIL-DTL-38999 Series III	Connector dimension Dim Nominal	-				
-Shell Material : Composite	ØS 29.4 Max	]	SOURIAU shall not be liable for any non-o	conformity or damage		
-Shell Plating : Nickel	Z' 31.5 Max VV THREAD M18x1-6g	-	due to a use of the Products which does not comply with			
-Insulator : Thermoplastic		-	the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)			
-Contacts : Copper Alloy			(professional recommendation, te			
-Seals & Grommet : Silicon Elastomer			Country         Jurisdiction & Control List           FR         Not Listed			
-Contact Plating : Gold over copper Alloy 0.8μm minimum			FR Not Listed			
-Durability : 500 Mating cycles			PN: 8D513M08BB			
-Delivered with Souriau contacts and Accessories						
-Temperature Range -65°C to +200°C		A 18-10-201	6 First Release			
-Salt Spray : 2000 hours Mass : 22.8 g ± 10%		ISS DATE	Latest modification - by		MOD N°	
– -Mass : 22.8 g ± 10%		Designed By:	Date:	CUSTOMER DRAWING		
		TITLE	TITLE Composite Plug 8D series			
BASIC SERIES: 8D 5 - 13 M	1 08 B B	SCALE	General linear	NPRDS / PROJECT		
	1 08 B B		-[ -(	859		
SHELL TYPE : Plug with RFI Shielding		NA		This document is the pro	operty of	
CONTACT TYPE : Standard Crimp Contact		SOURIAU WWW.SOURIAU.COM SOURIAU it must not be reproduced or				
SHELL SIZE : 13	500 Matings)		communicated without pe	ermission		
		FORMAT	SOURIAU DR		SHEET	
PLATING : M = Nickel	CONTACT LA	A3	8D513M08B		1/2	

-	Ŧ	G	г п	m		0	
		Contact Layout					
4		$ \begin{pmatrix} & & & & \\ & & & & \\ & & & & \\ & & & & \\ & & & & \\ & & & & \\ & & & & \\ & & & & \\ & & & & \\ & & & & \\ & & & & \\ & & & & \\ & & & & \\ & & & & \\ & & & & \\ & & & & \\ & & & & \\ & & & & \\ & & & & \\ & &$					
		Contacts (Insert arrangement 13-8)           Contact location           X-axis (mm)           X-axis (mm)           A         +.065 (1.65)         +.157 (3.99)           3         +.170 (4.32)         +.000 (0.00)           C         +.120 (3.05)        120 (3.05)           C        120 (3.05)        120 (3.05)           C        170 (4.32)         +.000 (0.00)           C        170 (4.32)         +.000 (0.00)           C        170 (4.32)         +.000 (0.00)           C        165 (1.65)         +.157 (3.99)           H         +.000 (0.00)         +.044 (1.12)					
ယ	Shell Arrangement Nu size no. cr 13 -8	mber of Size Service Contact Supersed ontacts contacts rating location 8 20 I All MS20051					
	-					SOURIAU shall not be liable for an due to a use of the Products wh the Specifications issued by either o (professional recommendat	
N						PN: 8D513N	
					A 18-10-20 ISS DATE Designed By:	16 First Release	
					SCALE	Compo General linear	
-					NA	Tolerances:	
					SOURIA	OURIAU WWW.SOURIAU.C	
				_	FORMAT A3	SOURIAU 8D513M	
	Н	G	F	E (	D	C	

