		т <u>С</u> т	m		0	ω	A		_
CHARACTERISTICS Servicer 1: Based on MIL-DTL 38299 Series II Schell Material Autminium Schell Material Autminium Schell Material Schell Material Schell Material Sche									4
Sundard : Based on MIL OTL 38999 Series II Shell Material :: Aluminium Shell Material :: Aluminium Shell Material :: Aluminium Shell Material :: Shell Material :: Aluminium Shell Material :: Shell :: Shell :: Shell :: Shell Material :: Shell Material :: Shell :: Shell :: Shell :: Shell :: Shell Material :: Shell Material :: Shell :									
-Salt Spray : 48 hours A 30-09-2016 First Release ISS DATE Latest modification - by MOD N° Designed By: Date: CUSTOMER DRAWING Designed By: Date: CUSTOMER DRAWING TITLE Aluminium Receptacle 8D series SCALE CONTACT TYPE : Jam nut Receptacle CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 19 PLATING : F = Nickel CONTACT TYPE : PIN(500 Matings) CONTACT TYPE : PIN(500 Matings) CONT	N	-Standard : Based on NIL-DTL-38999 Series III-Shell Material: Aluminium-Shell Plating: Nickel-Insulator: Thermoplastic-Contacts: Copper Alloy-Seals & Grommet: Silicon Elastomer-Contact Plating: Gold over copper Alloy 0.8μm minimum-Durability: 500 Mating cycles	DimNominalA49.2±0.3B33.32+0.1/-0.15R32.5MaxS46±0.4W3+0.9/-0.1		due to a use of the Pro the Specifications issued by (professional recor	ducts which does not cor either of the Parties or b nmendation, technical no Country Jurisdi FR	nply with y a third party otice.) ction & Control List		2
BASIC SERIES: 8D 7 19 F 28 P N L SCALE SCALE Ceneral linear NPRDS / PROJECT 859 1 SHELL TYPE : Jam nut Receptacle Standard Crimp Contact ORIENTATION : N NR Image: Standard Crimp Contact 859 1 SHELL SIZE : 19 CONTACT TYPE : PIN(500 Matings) CONTACT TYPE : PIN(500 Matings) NWW.SOURIAU.COM Image: Standard Crimp Contact SOURIAU SOURIAU SOURIAU 1 PLATING : F = Nickel CONTACT TYPE : PIN(500 Matings) CONTACT TYPE : PIN(500 Matings) FORMAT SOURIAU DRG N° SHEET 1/2								MOD N°	
BASIC SERIES. BU / - IS P						ninium Receptaclo			
A3 8D719F28PNL-C 1/2		SHELL TYPE : Jam nut Receptacle CONTACT TYPE : Standard Crimp Contact	Delivered W/O Co ORIENTATIO	ntacts NA		ances: 	859 This document is the pro SOURIAU it must not be reproduc	ced or	1
			CONTACT LAYOUT :	19-28			Λ		

ſ	т	G	г	m		C	Þ		,
4		Contact Layout				Panel cutout JAM NUT RECEPTACLE (TYPE 7)			4
	$\begin{array}{c c} & & & & & & \\ & & & & & & \\ & & & & & $								_
ω	ID (mm) A + 066 (1.68) B + 189 (4.80) C + 286 (7.26) D + 345 (8.76) E + 357 (9.07) F + 321 (8.15) G + 242 (6.15) H + 130 (3.30) J + 000 (0.00) K - 130 (3.30) L - 242 (6.15) M - 357 (9.07) P - 345 (8.76) Shell Arrangement N	$\begin{array}{c c c c c c c c c c c c c c c c c c c $				Dim Nominal B 33.91+0/-0.25 ØC 35.18+0.25/-0			3
	L								
	•					SOURIAU shall not be liable for any non-cor due to a use of the Products which does the Specifications issued by either of the Part (professional recommendation, tech	not comply with es or by a third party		
\sim						CountryJurisdiction & Control ListFRNot Listed			2
			PN: 8D719F28PNL						
					A 30-09-2016 First Release				-
					ISS DATE	Latest modification - by		MOD N°	-
						Designed By: Date: CUSTOMER DRAWING TITLE Aluminium Receptacle 8D series			
					SCALE	General linear Tolerances:	NPRDS / PROJECT 859		
→					SOURIAU	NA ± COS SOURIAU WWW.SOURIAU.COM This document is the prop SOURIAU it must not be reproduce communicated without per			1
					FORMAT	SOURIAU DRG	N°	SHEET	-
		-			A3	8D719F28PNL		2/2	
	Н	G	I F	I E	D	C B	A		