
т	۵	н п	m	C C







LAYOUT SHOWN AS

Keying Shown as example

CHARACTERISTICS

ယ

 \sim

-Mass

BASIC SERIES:

SHELL SIZE : 11

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

PLATING : J = Olive drab Cadmium

-Standard : Based on MIL-DTL-38999 Series III

-Shell Material	: Composite			
-Shell Plating	: Olive drab Cadmium			
-Insulator	: Thermoplastic			
-Contacts	: Copper Alloy			
-Seals & Grommet	: Silicon Elastomer			
-Contact Plating	: Gold over copper Alloy $0.8 \mu m$ minimum			
-Durability	: 500 Mating cycles			
-Delivered with Souriau contacts and Accessories				
-Temperature Range	_∶ -65°C to +175°C			
-Salt Spray	: 2000 hours			

: 11.6 g ± 10%

8D 0

G

11

J

22

В


F

С

Connector dimension			
Dim	Nominal		
Р	3.25±0.2		
PP	4.93±0.2		
R1	20.62		
R2	18.26		
S	26.2±0.3		
V	19.5+1.4/-0		
W'	2.1/3.65		
Ζ'	32 Max		
VV THREAD	M15x1-6g		

Е

SOURIAU shall not be liable for due to a use of the Products the Specifications issued by either (professional recommend



σ		A				
				4		
S EXAMPLE				3		
any non-conformi which does not co of the Parties or l ndation, technical n	mply with by a third party	1				
untry Jurisc FR	Jurisdiction & Control List Not Listed					
1J22BC						
			MOD N°			
	CUSTOMER	DRAWING				
ite Receptac	e Receptacle 8D series					
ar	NPRDS / F 85			1		
J.COM	COM This document is the property of SOURIAU it must not be reproduced or communicated without permission					
U DRG N°						
LJ22BC-C		A	1/2	J		
_						

4	(Contact Layout 22*				S A Tax	QUARE FLANGE RECEPTACLE REAR MOUNTING	Panel Cu
	Ctc A B	4#22D 11-22 X Y 1.905 1.905 1.905 -1.905				V		ØT
ω	C D	-1.905 -1.905 -1.905 1.905						Dim ØA ØAA R1 ØT
							the Specifications	of the Products
N							I	PN: 8D01
_					A ISS Designe	DATE	6 First Release Latest modificatio Date:	on - by
<u> </u>					SCA N/			General linear Tolerances: ±
					FORM		www	.souriau Souria
					A	3		8D011
	Н	G	F	E	D		С	

Т

ш

т

G

0

