

т	۵	п	m	0







LAYOUT SHOWN AS

Keying Shown as example

CHARACTERISTICS

BASIC SERIES:

SHELL SIZE : 19

PLATING : F = Nickel

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

ယ

 \sim

-Standard : Based on MIL-DTL-38999 Series III

-Shell Material : Aluminium : Nickel -Shell Plating -Insulator : Thermoplastic -Contacts : Copper Alloy : Silicon Elastomer -Seals & Grommet -Contact Plating : Gold over copper Alloy 0.8µm minimum -Durability : 500 Mating cycles -Delivered with Souriau contacts and Accessories : -65°C to +200°C -Temperature Range : 48 hours -Salt Spray -Mass : 31.07 g ± 10%

8D 0

G

19

F

11

А

F

Ν

P 3.25±0.2 PP 4.93±0.2 R1 29.36 R2 26.97 S 36.5±0.3 V 20.83+0/-1.25 W 2.1/2.5 Z 31.5 Max		dimension
PP 4.93±0.2 R1 29.36 R2 26.97 S 36.5±0.3 V 20.83+0/-1.25 W 2.1/2.5 Z 31.5 Max	Dim	Nominal
R1 29.36 R2 26.97 S 36.5±0.3 V 20.83+0/-1.25 W 2.1/2.5 Z 31.5 Max	Р	3.25±0.2
R2 26.97 S 36.5±0.3 V 20.83+0/-1.25 W 2.1/2.5 Z 31.5 Max	PP	4.93±0.2
S 36.5±0.3 V 20.83+0/-1.25 W 2.1/2.5 Z 31.5 Max	R1	29.36
V 20.83+0/-1.25 W 2.1/2.5 Z 31.5 Max	R2	26.97
W 2.1/2.5 Z 31.5 Max	S	36.5±0.3
Z 31.5 Max	V	20.83+0/-1.25
	W	2.1/2.5
VV THREAD M28x1-6g	Z	31.5 Max
	VV THREAD	M28x1-6g

ORIENTATION : N

CONTACT TYPE : PIN(500 Matings)

Е

CONTACT LAYOUT : 19-11

SOURIAU shall not be liable for due to a use of the Products the Specifications issued by either (professional recomment



σ		Þ			
R				4	
AS EXAMPLE				3	
r any non-conformi s which does not co er of the Parties or ndation, technical r untry Juriso FR 9F11AN	omply with by a third part			2	
			MOD N°		
um Receptac	CUSTOMER DRAWING n Receptacle 8D series NPRDS / PROJECT 859				
This document is the property of SOURIAU it must not be reproduced or communicated without permission SHEET					
F11AN-C			1/2		
B		A		J	

