





## NOTES:

## MATERIALS:

- 1. BODY = STAINLESS STEEL PER ASTM A582, ALLOY 303, CONDITION "A".
  2. INSULATOR = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
  3. CONTACT = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.

## FINISHES:

- BODY = GOLD PLATE PER ASTM B488-11, TYPE II, 30µin MIN, GRADE C, OVER 50 TO 100µin STRESS FREE NICKEL PER AMS-QQ-N-290.
   CONTACT = GOLD PLATE PER ASTM B488-11, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN: D.N. CHKD:	DATE 12/16/15 DATE		,	Property of Rac this document cannot be re- communicated to a third par	produced or	
DECIMAL	ANGLE	N.D.	12/16/15	a RADIALL companywritten permission of RADIALL.  SMA STRAIGHT JACK				
		APVD:	DATE	4 HOLE FLANGE MOUNT DIRECT SOLDER TYPE				
		J.M.	12/16/15	FOR .085 S/R & SIMILAR CABLES				
REFERENCE:		MATERIALS & FIN	ISHES:	SIZE	FSCM NO.	DWG NO.	7 010	REV
ORIGINATED: D.N.		SEE NOTES		А	19505	9431-158	33-010	Α
DATE: 12/16/15				SCALE 4:1		THIRD ANGLE PROJECTION	SHEET 1 C	)F 1