

FFA.3E.250.CLAC85Z

SUMMARY

Wires

Coax 1



Image is for illustrative purpose only

Series 3E

Termination type Male solder Coaxial

IP rating 68 mated (mating interface)

AWG wire size 0.00 - 0.00

Cable Ø 8.10 - 8.50 mm

Status Active

Matching parts ERA.3E.250.CTL

Download

Request a quote

Catalog

TECHNICAL DETAILS

Mechanics

Shell Style/Model FFA*: Straight plug, cable collet and nut for fitting a bend relief

Keying Circular, male

Housing Material

Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE

AMS QQ N 290] brass mid pieces

Variant Z: Nut for fitting a bend relief

Weight 71.41 g

Performance

 Configuration
 3E.250 : 1 Coax (50 Ohm)

 Insulator
 L: PEEK (UL 94 / V-0/1.5)

Rated Current 26 Amps

Specifications

Contact Type: Solder

Vtest: 3000 V (AC), 4200 V (DC)

Impedance: 50 Ohm VSWR: 1.06 + 0.5 * f/GHz

Cable type: RG 213/U, RG 115 A/U, RG 11 A/U, RG 144/U, RG 165 /U

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Others

Endurance (Shell): 5000 mating cycles Temp (min / max): -55°C / +200°C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [6 ms] Climatical Category: 50/175/21 Shielding (min): 95 dB (10 MHz) Shielding (min): 80 dB (1 GHz) Salt Spray Corrosion: >1000 hr

DRAWINGS



Dimensions

	А	L	М	S2
mm.	19	60	40	15
in.	0,75	2,36	1,57	0,59

RECOMMENDED BY LEMO

Tools

Spanner wrench: DCD.3E.ZZZ.PA150
Caps: BFA.3E.100.NAS

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

