

# AM23SGD3-F

SOT-23 Surface Mount LED Lamp



# **DESCRIPTION**

• The Super Bright Green source color devices are made with Gallium Phosphide Green Light Emitting


### **FEATURES**

- SOT-23 package surface mount LED lamp
- · Low power consumption
- · Long life solid state reliability
- Package: 2000 pcs / reel
- Moisture sensitivity level: 3
- Halogen-free
- · RoHS compliant

### **APPLICATIONS**


- Backlight
- · Status indicator
- · Home and smart appliances
- · Wearable and portable devices
- · Healthcare applications

# **PACKAGE DIMENSIONS**



### RECOMMENDED SOLDERING PATTERN

(units: mm; tolerance: ± 0.1)



- Notes:

  1. All dimensions are in millimeters (inches).

  2. Tolerance is ±0.25(0.01") unless otherwise noted.

  3. Lead spacing is measured where the lead emerge from the package.

  4. The specifications, characteristics and technical data described in the datasheet are subject to change
- without prior notice.

  5. The device has a single mounting surface. The device must be mounted according to the specifications.

## **SELECTION GUIDE**

Part Number	Emitting Color	Lens Type	Iv (mcd) @ 20mA [2]		Viewing Angle [1]
Fait Number	(Material)	Lens Type	Min.	Тур.	201/2
AM23SGD3-F	Super Bright Green (GaP)	Green Diffused	3	8	170°

Notes.

1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.

2. Luminous intensity / luminous flux: +/-15%.

3. Luminous intensity value is traceable to CIE127-2007 standards.



# ELECTRICAL / OPTICAL CHARACTERISTICS at T<sub>A</sub>=25°C

Parameter	Symbol	Emitting Color	Value		Unit
Farameter	Symbol	Emitting Color	Тур.	Max.	Ollit
Wavelength at Peak Emission I <sub>F</sub> = 20mA	$\lambda_{peak}$	Super Bright Green	565	-	nm
Dominant Wavelength I <sub>F</sub> = 20mA	λ <sub>dom</sub> <sup>[1]</sup>	Super Bright Green	568	-	nm
Spectral Bandwidth at 50% $\Phi$ REL MAX I <sub>F</sub> = 20mA	Δλ	Super Bright Green	30	-	nm
Capacitance	С	Super Bright Green	15	-	pF
Forward Voltage I <sub>F</sub> = 20mA	V <sub>F</sub> <sup>[2]</sup>	Super Bright Green	2.2	2.5	V
Reverse Current (V <sub>R</sub> = 5V)	I <sub>R</sub>	Super Bright Green	-	10	μА
Temperature Coefficient of $\lambda_{\text{peak}}$ $I_F$ = 20mA, -10°C $\leq T \leq 85^{\circ}C$	$TC_{\lambda peak}$	Super Bright Green	0.12	-	nm/°C
Temperature Coefficient of $\lambda_{dom}$ I <sub>F</sub> = 20mA, -10°C $\leq$ T $\leq$ 85°C	$TC_{\lambdadom}$	Super Bright Green	0.08	-	nm/°C
Temperature Coefficient of $V_F$ $I_F$ = 20mA, -10°C $\leq$ T $\leq$ 85°C	TC <sub>V</sub>	Super Bright Green	-2	-	mV/°C

### Notes:

Notes:

1. The dominant wavelength (\(\lambda\)d) above is the setup value of the sorting machine. (Tolerance \(\lambda\)d: \(\pm\)1nm.)

2. Forward voltage: \(\pm\)2.1V.

3. Wavelength value is traceable to CIE127-2007 standards.

4. Excess driving current and \(\forall \) or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.

# ABSOLUTE MAXIMUM RATINGS at T<sub>A</sub>=25°C

Parameter	Symbol	Value	Unit
Power Dissipation	$P_{D}$	62.5	mW
Reverse Voltage	V <sub>R</sub>	5	V
Junction Temperature	Tj	110	°C
Operating Temperature	T <sub>op</sub>	-40 to +85	°C
Storage Temperature	T <sub>stg</sub>	-40 to +85	°C
DC Forward Current	I <sub>F</sub>	25	mA
Peak Forward Current	I <sub>FM</sub> <sup>[1]</sup>	140	mA
Electrostatic Discharge Threshold (HBM)	-	8000	V
Thermal Resistance (Junction / Ambient)	R <sub>th JA</sub> <sup>[2]</sup>	530	°C/W
Thermal Resistance (Junction / Solder point)	R <sub>th JS</sub> [2]	430	°C/W


Notes:
1. 1/10 Duty Cycle, 0.1 ms Pulse Width.
2.  $R_{\text{In Ja}}$ ,  $R_{\text{In Ja}}$ ,  $R_{\text{In Ja}}$  Results from mounting on PC board FR4 (pad size  $\geq$  16 mm<sup>2</sup> per pad).
3. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.






### **TECHNICAL DATA**


### **RELATIVE INTENSITY vs. WAVELENGTH**





# **SPATIAL DISTRIBUTION**




# **SUPER BRIGHT GREEN**










## **REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS**




- Notes.

  1. Don't cause stress to the LEDs while it is exposed to high temperature.


  2. The maximum number of reflow soldering passes is 2 times.

  3. Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product

### TAPE SPECIFICATIONS (units: mm)





## **REEL DIMENSION** (units: mm)





# **PACKING & LABEL SPECIFICATIONS**





### **PRECAUTIONARY NOTES**

- The information included in this document reflects representative usage scenarios and is intended for technical reference only.
- The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
- When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.

  The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening
- liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright. All design applications should refer to Kingbright application notes available at <a href="https://www.KingbrightUSA.com/Application">https://www.KingbrightUSA.com/Application</a>

