


Oct.1.2023 Copyright 2023 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△	1	RE-F-06478	J.M	M. 99.7.29	△				
△					△				
APPLICATION STANDARD									
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C			STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C			
	VOLTAGE	AC 50 V			OPERATING HUMIDITY RANGE	RELATIVE HUMIDITY 95 % MAX (NO DEW CONDENSATION IS PERMITTED);			
	CURRENT	0.3 A							
SPECIFICATIONS									
ITEM		TEST METHOD			REQUIREMENT			QT	AT
CONSTRUCTION									
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT			ACCORDING TO DRAWING			○	○
MARKING		CONFIRMED VISUALLY.						○	○
ELECTRICAL CHARACTERISTICS									
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).			60 mΩ MAX			○	○
INSULATION RESISTANCE		100 V DC			100 MΩ MIN			○	—
VOLTAGE PROOF		150 V AC FOR 1 min.			NO FLASHOVER OR BREAKDOWN.			○	○
MECHANICAL CHARACTERISTICS									
INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.			INSERTION FORCE 40.8 N MAX WITHDRAWAL FORCE: 1.7 N MIN.			○	—
MECHANICAL OPERATION		50 TIMES INSERTION AND EXTRACTIONS.			1)CONTACT RESISTANCE: 70 mΩ MAX 2) NO DAMAGE, CRACK AND LOOSENESS OF PART			○	—
VIBRATION		FREQUENCY: 10 TO 55 Hz, SINGLE AMPLITUDE: 0.75 mm, — m/s ² AT 10 CYCLES FOR 3 DIRECTIONS.			1)NO ELECTRICAL DISCONTINUITY OF 1 μs MIN. 2)NO DAMAGE, CRACK AND LOOSENESS OF PART.			○	—
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.						○	—
ENVIRONMENTAL CHARACTERISTICS									
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90~95 %, 96 h			1)CONTACT RESISTANCE: 70 mΩ MAX. 2)INSULATION RESISTANCE: 100 MΩ MIN.			○	—
RAPID CHAGE OF TEMPERTURE		TEMPERTURE -55→15~35→ 85→15~35°C TIME 30→ 2~ 3→ 30→ 2~ 3 min. UNDER 5 CYCLES.			3)NO DAMAGE, CRACK AND LOOSENESS OF PART			○	—
DRY HEAT		EXPOSED AT 85 °C, 96 h.			1)CONTACT RESISTANCE: 70 mΩ MAX.			○	—
COLD		EXPOSED AT -55 °C, 96 h.			2)NO DAMAGE, CRACK AND LOOSENESS OF PART.				
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.			NO HEAVY CORROSION.			○	—
SULPHUR DIOXIDE		EXPOSED IN 10 PPM FOR 96 h (TEST STANDARD:JIS C 0090)			1)CONTACT RESISTANCE: 70 mΩ MAX. 2)NO HEAVY CORROSION.			○	—
RESISTANCE TO SOLDERING HEAT		REFLOW RECOMMENDED TEMPERATURE PROFILE  TO BE TESTED UNDER THE ABOVE CONDITIONS			NO MELTING OF RESIN WHICH AFFECTS THE PERFORMANCE OF COMPONENT.			○	—
SOLDRABILITY		SOLDERED AT SOLDER TEMPERATURE. 235 °C FOR IMMERSION DURATION, 2 s.			NO PINHOLE OR DEWETTING ON SOLDERED SURFACE			○	—
REMARKS				DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
				S Kitajima 99.05.25	J Matsukawa 99.05.25	M.Ishida 99.05.26	Y Yoshimura 99.05.27		
UNLESS OTERWISE SPECIFIED ,REFER TO JIS C 5402.									
NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST ○ APPLICABLE TEST									
HRS HIROSE ELECTRIC CO. LTD.		SPECIFICATION SHEET			PART NO. FX11LB - 68P - SV				
CODE NO.(OLD): CL		DRAWING NO ELC4 - 152104 -			CODE NO CL 573 - 0052 -5			1	1

TO
PCK