






APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/23/05	
A		CHANGED INSULATOR MATERIAL	8/13/09	
B		REVISED SPEC.	05/09/12	
C		REDRAWN	2/6/14	HR/KW



FPC/FFC T = .012 ± .002 [0.30 ± 0.05]

**SPECIFICATIONS:**

- Material: Insulator: Hi-Temp Thermoplastic, rated UL 94V-0
- Insulator color: Black
- Contacts: Phosphor Bronze
- Plating: Tin over Nickel underplate overall
- Electrical: Operating voltage: 50 VAC max
- Current rating: 0.5 Amps max
- Contact resistance: 30 mohms max initial
- Insulation resistance: 500 Mohms min
- Dielectric withstanding voltage: 500 VAC for 1 minute
- Temperature Rating: Operating temperature: -20°C to +85°C
- Environmental: Lead free, RoHS compliant

Positions: 3 thru 30  
 A = .039 [1.00] x No. of Spaces  
 B = A + .083 [2.10]  
 C = A + .157 [4.00]

UNLESS OTHERWISE SPECIFIED  
 ALL DIMENSIONS ARE INCHES [MM]  
 TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

**ADAM TECH**

909 Railway Avenue, Union, NJ 07083  
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: LIF FLEX CIRCUIT CONNECTOR  
 TOP ENTRY, .079 [2.00] ROW SPACING

APPROVALS	DATE
DRAWN SS	3/23/05
CHECKED AY	7/28/10
APPROVED	

SIZE	PART NO.	REV.
X	PGB-C-XX-T-20	C

REF: S00043T SCALE: NTS SHEET 1 OF 1

