

Sep. 1. 2023 Copyright 2023 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				

APPLICABLE STANDARD			
POWER	2 W	CHARACTERISTIC IMPEDANCE	50 Ω
OPERATING TEMPERATURE RANGE	-40°C TO +85 °C	STORAGE TEMPERATURE RANGE	-40°C TO +70 °C
FREQUENCY RANGE	DC TO 6000 MHz	OPERATING HUMIDITY RANGE	% TO 90 %
CURRENT		APPLICABLE CABLE	


SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	×	×
MARKING	CONFIRMED VISUALLY.		-	-

ELECTRIC CHARACTERISTICS					
VSWR	FREQUENCY DC TO 3000 MHz.	1.25	MAX	×	-
	※1 FREQUENCY 3000 TO 6000 MHz.	1.4	MAX		
INSERTION LOSS	FREQUENCY DC TO 3000 MHz.	0.3dB	MAX	×	-
	※1 FREQUENCY 3000 TO 6000 MHz.	0.5dB	MAX		
ISOLATION	FREQUENCY TO MHz.		MIN	-	-
CONTACT RESISTANCE	VALUE AT MAXIMUM OF DC 100 mA	CENTER	30 mΩ MAX	×	-
		OUTER	30 mΩ MAX		
INSULATION RESISTANCE	VALUE AT DC 100 V MIN.	1000	MΩ MIN	×	-
VOLTAGE PROOF	MUST KEEP THE AC 100 V FOR 1 min.	NO FLASHOVER OR BREAKDOWN.		×	×

MECHANICAL CHARACTERISTICS					
DURABILITY	MUST BE LESS THAN THE STD.VALUE AFTER 500 TIMES INSERTION AND EXTRACTIONS AT THE CONDITION.	① CONTACT RESISTANCE: CENTER 30 mΩ MAX OUTER 30 mΩ MAX		×	-
		② JUST NOT HAVE HEAVY CORROSION.			



REMARKS	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
※1 : This spec is under mated condition with MS-156-HRMJ-3.	<i>K. Hida</i>	<i>K. Hida</i>	<i>K. Kawamura</i>	<i>Y. Nishida</i>	
Unless otherwise specified, refer to IEC-60512.	03.5.23	03.5.23	03.5.23	03.5.24	

Note QT:Qualification Test AT:Assurance Test ×:Applicable Test

HRS HIROSE ELECTRIC CO., LTD.	SPECIFICATION SHEET	PART NO.	MS-156R-HRMJ-1
	CODE NO.(OLD) CL	DRAWING NO. ELC4 -180354	PART NO. CL358-0188-8

1 / 1

TO
RFD

