






STRAIGHT PLUG CRIMP TYPE CABLE 2.6/50 D

PAGE 1/2 ISSUE 01-07-15B SERIES SMA PART NUMBER R125072080







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)	
Body	STAINLESS STEEL.	GOLD 0.5 OVER NICKEL 2	
Center contact	BRASS	GOLD 1.3 OVER NICKEL2	
Outer contact	-	-	
Insulator	PTFE		
Gasket	SILICONE RUBBER		
Others parts	STAINLESS STEEL.	GOLD 0.5 OVER NICKEL 2	
-	-	-	
-	-	-	



Technical Data Sheet

STRAIGHT PLUG CRIMP TYPE CABLE 2.6/50 D

PAGE **2/2** ISSUE 01-07-15B SERIES SMA PART NUMBER R125072080

PACKAGING

100	Contact us	Contact us
Standard	Unit	Other

ELECTRICAL CHARACTERISTICS

Impedance 50 Frequency 0-12.4 GHz **VSWR** 1.15 0,0200 x F(GHz) Maxi √F(GHz) dB Maxi Insertion loss 0.06 RF leakage 60 - F(GHz)) dB Maxi - (Voltage rating Veff Maxi 250 Dielectric withstanding voltage 750 Veff mini Insulation resistance 5000 $M\Omega$ mini

MECHANICAL CHARACTERISTICS

Center contact retention

Axial force - Mating End NA N mini Axial force - Opposite end 27 N mini N.cm mini Torque NA

Recommended torque

100 Mating N.cm Panel nut NA N.cm Clamp nut NA N.cm A/F clamp nut 0,0000 mm

Mating life 500 Cycles mini g

Weight 3,1060

ENVIRONMENTAL

-65/+165 Operating temperature °С Hermetic seal NA Atm.cm3/s Panel leakage NA

SPECIFICATION

CABLE ASSEMBLY

Stripping	а	b	С	d	е	f
mm	2	7	9	0	7	0

Assembly instruction:

Recommended cable(s)

K02252D **RD 316 ECO 316 D**

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the assembly

Cable retention

- pull off 110 N mini - torque NA N.cm

TOOLING

Part Number	Description	Hexagon
R282271000	CRIMPING TOOL	3.84
R282293000	CRIMPING TOOL M22520/5-01	-
R282235037	CRIMPING DIES	3.84

OTHER CHARACTERISTICS