





COAXIAL TERMINATION 7-16 FEMALE 6 GHZ 30W

PAGE 1/2 ISSUE 07-11-19B SERIES TERMINATION PART NUMBER R404757000





All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)	
Body Center contact Outer contact Insulator Gasket	BRASS BERYLLIUM COPPER BRASS PTFE	BBR2 GOLD 0.5 OVER NICKEL PHOSPHORUS 2 SILVER 5 PASSIVATED OVER COPPER 0.5	
Substrate Resistor Others parts	ALUMINIUM NITRIDE THICK FILM ALUMINIUM	BLACK ANODIZATION	





COAXIAL TERMINATION 7-16 FEMALE 6 GHZ 30W

PAGE 2/2	ISSUE 07-11-19B	SERIES TERMINATION	PART NUMBER R404757000
-----------------	-----------------	-----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 3	3 - 6
V.S.W.R (≤)	1.20	1.40

DC - 6	GHz
50	Ω
50	Ω ± 5%
2000	W
30	W (Free Air Cooled)
	W (Conduction Cooled)
	50 50 2000


MECHANICAL CHARACTERISTICS

Connectors	7-16	Female	IEC 169-4
Weight	239,2700 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS

MOUNTED WITH VERTICAL COOLING FINS AND NATURAL CONVECTION