# **Technical Data Sheet**



SP4T Terminated Ramses SMA 18GHz Latching 28Vdc TTL Diodes D-sub connector

PAGE 1/2 ISSUE 11-04-17 SERIE : SPnT PART NUMBER : R574423425

### RF CHARACTERISTICS

Number of ways : 4

Frequency range : 0 - 18 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18
VSWR max	1.20	1.30	1.40	1.50
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB
Isolation min	80 dB	70 dB	60 dB	60 dB
Average power (*)	240 W	150 W	120 W	100 W

TERMINATION IMPEDANCE : 50 Ohms

TERM. AVG. POWER AT 25° C : 1 W per termination / 3 W total power

### **ELECTRICAL CHARACTERISTICS**

Actuator : LATCHING

Nominal current \*\* : 125 mA / RESET : 500 mA \*\*\*\*

Actuator voltage (Vcc) : 28V (24 to 30V)

Terminals : 25 pins D-SUB male connector TTL inputs (E) - High level : 2.2 to 5.5 V / 800µA at 5.5 V

- Low level : 0 to 0.8 V / 20µA at 0.8 V

## MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012 Life : 2 million cycles per position

Switching Time\*\*\* : <15 ms

Construction : Splashproof

Weight : < 250 g

## **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(\* Average power at 25°C per RF Path)

(\*\* At 25° C ±10%)

(\*\*\* Nominal voltage; 25° C)

(\*\*\*\* Reset : supply voltage time 1sec. max. / duty cycle 10%)




# **Technical Data Sheet**




SP4T Terminated Ramses SMA 18GHz Latching 28Vdc TTL Diodes D-sub connector


PAGE 2/2 ISSUE 11-04-17 SERIE : SPnT PART NUMBER : R574423425

### **DRAWING**




TTL input	RF Continuity		
RESET = 1	All ports open		
E1 = 1	$IN \leftrightarrow 1$		
E2 = 1	$IN \leftrightarrow 2$		
E3 = 1	$IN \leftrightarrow 3$		
E4 = 1	$IN \leftrightarrow 4$		





General tolerances :  $\pm 0.5$  mm [0,02 in]

# SCHEMATIC DIAGRAM



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.