



Main

| | |
|-------------------------------|---------------------|
| Range of Product | L100/300 |
| Series name | Severe duty foundry |
| Product or Component Type | Limit switch |
| Product Specific Application | Foundry switch |
| Device short name | L100 L300 |
| Body type | Fixed |
| Head type | Rotary head |
| Sale per indivisible quantity | 1 |

Complementary

| | |
|--|--|
| Base plate style | Style 2 |
| Body Material | Cast aluminium |
| Fixing Mode | By the body |
| Type of operator | Spring return without operating lever |
| Contact sequence number | 18 |
| Function Available | Neutral position |
| Switch actuation | From left or right CW and CCW |
| Type of approach | Lateral approach |
| Electrical connection | Screw-clamp terminals AWG 22...AWG 12 |
| Cable entry | 1 entry for 1/2" - 14 NPT ANSI B1.20.1 |
| Number of poles | 2 |
| Contacts type and composition | 2 NC |
| CW operation contacts | 1 NO + 1 NC |
| CCW operation contacts | 1 NC + 1 NO |
| Contacts style | B |
| Switch Function | DPST-NC-DB |
| Contact form | Form YY |
| Contacts material | 90/10 AgCdO on copper backing stationary contact Silver on steel backing moveable contact |
| Contacts usage | - |
| Contact operation | Slow-break, break before make |
| Positive opening | Without |
| Minimum torque for tripping | 95 ozf.in |
| Maximum actuation speed | 90 Ft/Min with 45° cam angle, levers only 130 ft/min with 30° cam angle, levers only |
| Tripping angle | 7 ° |
| Maximum displacement angle | 70 ° |
| Contact code designation | A600, AC (Ue = 600 V) Ie = 1.2 A NEMA rating designation A600, AC (Ue = 480 V) Ie = 1.5 A NEMA rating designation A600, AC (Ue = 240 V) Ie = 3 A NEMA rating designation A600, AC (Ue = 120 V) Ie = 6 A NEMA rating designation |
| [Ithe] conventional enclosed thermal current | 20 A |
| [Ui] rated insulation voltage | 600 V 3)IEC 60947-1 600 V 3)UL 508 600 V 3)CSA C22.2 No 14 |

| | |
|--|---|
| [Uimp] rated impulse withstand voltage | 2.5 KV AC for 1 minute CE 2.2 KV AC for 1 minute UL 2.64 kV AC for 1 minute CSA |
| Short-circuit protection | 20 A Bussmann class CC KTK-R-20 non-time delay |
| Width | 2.25 in (57.15 mm) |
| Height | 4.95 in (125.73 mm) |
| Depth | 2.03 in (51.56 mm) |
| Net Weight | 1.5 lb(US) (0.68 kg) |
| Terminals description ISO n°1 | (1-2) left side contact (3-4) right side contact |

Environment

| | |
|---------------------------------------|--|
| Shock resistance | 30 gn 9 ms IEC 60068-2-27 |
| Vibration resistance | 10 gn 10...55 Hz)IEC 60068-2-6 |
| NEMA degree of protection | NEMA 1 Nema type 250 NEMA 2 Nema type 250 NEMA 4 Nema type 250 NEMA 12 Nema type 250 NEMA 13 Nema type 250 |
| IP degree of protection | IP67 conforming to IEC 60529 |
| Electrical shock protection class | Class 0 IEC 61140 |
| Ambient Air Temperature for Operation | -10...185 °F (-23...85 °C) |
| Ambient Air Temperature for Storage | -10...185 °F (-23...85 °C) |
| Protective treatment | Corrosion resistant gray paint |

Ordering and shipping details

| | |
|-----------------------|-----------------------------|
| Category | 22426-LIMIT SWITCHES,TYPE L |
| Discount Schedule | DS1 |
| GTIN | 785901079040 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 24.00 oz (680.389 g) |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------------|----------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 12.70 in (32.258 cm) |
| Package 1 width | 5.00 in (12.7 cm) |
| Package 1 Length | 32.26 in (81.935 cm) |

Offer Sustainability

| | |
|---------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|