

SBA0520Q ~ SBA0540Q Series Extreme Low V_F Schottky Rectifier

Current

0.5 A

Voltage

Features


• Ultra low forward voltage, low power loss

20~40 V

- Surface mount package
 Lead free in compliance with EU RoHS 2.0
- Lead free in compliance with EU ROHS 2.0
 Green molding compound as per IEC 61249 standard

Mechanical Data

- Case : DFN1006-2L Package
- Terminals : Solderable per MIL-STD-750, Method 2026
- Approx. Weight : 0.0006 grams



Maximum Ratings ($T_A = 25 \degree C$ unless otherwise noted)

PARAMETER	SYMBOL	SBA0520Q	SBA0530Q	SBA0540Q	UNIT	
Maximum Repetitive Peak Reverse Voltage	Vrrm	20	30	40	V	
Maximum RMS Voltage	Vrms	14	21	28	V	
Maximum DC Blocking Voltage	V _R	20	30	40	V	
Maximum Average Forward Rectified Current	IF(AV)	0.5				
Peak Forward Surge Current : 8.3ms Single Half Sine- Wave Superimposed On Rated Load	IFSM	2				
Typical Thermal Resistance ^(Note 1)	R _{0JA}	430				
Operating Junction Temperature Range	TJ	-55 to +150				
Storage Temperature Range	T _{STG}	-55 to +150				

Electrical Characteristics

PARAMETER	SYMPO	TEST CO		SBA0520Q		SBA0530Q		SBA0540Q		
	SYMBOL	TEST CONDITION		TYP.	MAX.	TYP.	MAX.	TYP.	MAX.	UNIT
Forward Voltage		I _F = 10mA	TJ =25 °C	0.24	-	0.25	-	0.26	-	V
		I⊧ = 100mA		0.32	-	0.33	-	0.35	-	
	VF	I _F = 500mA		-	0.48	-	0.52	-	0.6	
		I _F = 10mA	T 405.00	0.13	-	0.13	-	0.15	-	
		I _F = 100mA	0.23	-	0.24	-	0.29	-	V	
Reverse Current ^(Note 2)		V _R = 10V	Tj=25°C	4.6	-	4	-	1.3	-	μΑ
		$V_R = 20V$		-	100	9	-	1.9	-	
		$V_R = 30V$		-	-	-	100	3.1	-	
	IR	$V_R = 40V$		-	-	-	-	-	50	
		V _R = 20V	T _J =125 °C	1.7	-	1.4	-	0.5	-	mA
		$V_R = 30V$		-	-	3.5	-	0.8	-	
	VR	$V_R = 40V$		-	-	-	-	1.3	-	


NOTES : 1. Mounted on a FR4 PCB, single-sided copper, mini pad.

2. Short duration pulse test used to minimize self-heating effect.



ė,

TYPICAL CHARACTERISTIC CURVES








Fig.3 Typical Reverse Characteristics









Fig.4 Typical Reverse Characteristics










Fig.7 Typical Forward Characteristics






March 30,2023



Product and Packing Information

Part No.	Package Type	Packing Type	Marking	Version
SBA0520Q	DFN1006-2L	10K pcs / 7" Reel	A7	Halogen free RoHS compliant
SBA0530Q	DFN1006-2L	10K pcs / 7" Reel	E7	Halogen free RoHS compliant
SBA0540Q	DFN1006-2L	10K pcs / 7" Reel	C7	Halogen free RoHS compliant

Packaging Information & Mounting Pad Layout





Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, noninfringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.