



10 mm Miniature Speaker - 8 Ohm

Part No: SPKM.10.8.A

Description:

10mm Miniature Speaker - 8 Ohm 500mW RMS
Compact design for integration in a wide range of products

Features:

8 Ohm Impedance

Rated Input Power 500mW RMS

Max Input Power 1W peak

High Sensitivity

Dimensions: Ø10 x 4 mm

Connector: Wire Lead

RoHS & Reach Compliant



1.	Introduction	3
2.	Specifications	4
3.	Speaker Measurement Conditions	6
4.	Speaker Characteristics	7
5.	Mechanical Drawing	8
6.	Packaging	9
	Changelog	10

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.











1. Introduction



Taoglas added miniature speakers to our product portfolio to provide both reliable connectivity and high-quality audio solutions from one trusted company. Featuring a compact design, enabling ease of integration in a wide range of electronics products, including IoT devices, with high levels of long-term reliability and best in class performance Taoglas products are known for.

Our 10 mm Miniature Speaker offers a frequency response of 100 Hz - 11 kHz and high sensitivity, with 8 Ohm impedance and power handling of 0.5W RMS and 1W peak. Proven performance in demanding applications where the accurate reproduction of voice communications is required.

Please contact your regional Taoglas customer support team for more information or installation guidelines.

The table below shows a guide to help select the best speaker for your application based on size requirements:

Dimensions
Ø10 x 3.5 mm
Ø15 x 3.7 mm
Ø17 x 4.4 mm
Ø20 x 4.3 mm
Ø23 x 6 mm
Ø28 x 5.1 mm
30 x 20 x 5.1 mm
24 x 13 x 8.7 mm
28 x 9 x 3.8 mm
Ø50 x 8.3 mm



2. Specifications

	Electroacoustic
Sound Pressure Level	75 dB SPL (± 3 dB) @ 1000 Hz (0 dB SPL = 20 μ Pa) Measuring Condition: 0.1 W (Sine wave) @ 0.05 m with baffle
Impedance	8Ω (±15%) @ 2 kHz with 1 V input signal and without baffle in place
Frequency Response	100 Hz - 11 kHz
Resonant Frequency	900 Hz (±20 %) Typical frequency @ 1 V
Nominal Input Power	500 milliwatts
Maximum Input Power	1 Watt
Distortion	Less than 10% @ 1 kHz, with input levels up to 1.75 V RMS
	Mechanical
Height	4 mm
Diameter	10 mm
Weight	0.004 Kg
Connector	Wire leads – 32 AWG (UL1571)
Material	PEI diaphragm with Neodymium Magnet, (without enclosure)
	Environmental
Temperature Range	-40°C to 80°C
Humidity	Non-condensing up to 95% Relative Humidity @ up to 65°C



	Reliability Testing	
High Tomporature Test	High Temp	+80°C (±2°C)
High Temperature Test	Duration	96 Hours
Low Temperature Test	Low Temp	-40°C (±2°C)
Low remperature rest	Duration	96 Hours
	High Temp	+75°C (±2°C)
	Low Temp	-40°C (±2°C)
Heat Shock Test	Changeover time	<30 Seconds
	Duration	1 Hour
	Cycle	100 cycles
	Temp	+40°C (±2°C)
Humidity Test	Relative Humidity	90 - 95 %
	Duration	96 Hours
	Temp	-40°C to +75°C
Temperature Cycle Test	Duration	45 minutes
remperature cycle rest	Temperature gradient	1°C to 3°C / minute
	Cycle	25 cycles
	Mounted with dummy set mass	0.8 g
Drop Test	Height	1 m
	Cycle	6 cycles
Load Test	White noise (EIA filter) for 96 hou	urs @ 0.5 W (1.25 V) input power
	White noise (EIA filter) for 1 minu	ute @ 0.8 W (1.75 V) input power

^{*} SPL (Sound Pressure Level) as specified did not deviate more than ±3 dB from initial value, with no significant damage after testing.




3. Speaker Measurement Conditions

3.1 Conditions

Standard Test Fi	xture Conditions
Input Power	0.5 Watts (2 V)
Mode	TSR
Potentiometer Range	50 dB
Sweep Time	0.5 seconds

3.2 Measurement Fixture Diagram






4. Speaker Characteristics

4.1


SPL

dBSPL vs. Frequency





5. Mechanical Drawing (Units: mm)



	Name	Material	Finish	QTY
1	ø10mm Frame	Fe	Zinc Plated—Blue White	1
2	ø5.7mm Voice coil	Cu	Natural	1
3	ø5.2x0.8mm Magnet	Nd-Fe-B	Zinc Plated	1
4	ø9.35mm Diaphragm	PEN	Natural	1
5	Gasket	T=1mm(Fe)	Zinc Plated—Blue White	1
6	UL1571 32AWG Lead wire	PVC	Black	1
7	UL1571 32AWG Lead wire	PVC	Red	1




6. Packaging

1 pcs SPKM.10.8.A per Blister Dimensions – 95 x 42 x 12mm

200 pcs SPKM.10.8.A per EPE Tray 6 Trays SPKM.10.8.A per Carton 7 pcs SPKM.10.8.A per Layer Board

1200 pcs SPKM.10.8.A per Carton Dimensions – 560 x 450 x 330mm





SPE-22-8-010 - SPKM.10.8.A

Revision: D	
Date:	18-11-2022
Changes:	Mechanical Drawings Updated to Rev D02
Changes Made by:	Carlos Gomes

Previous Revisions

Revision: A	
Date:	22-02-2022
Changes:	Initial release
Changes Made by:	Jack Conroy

Revision: B	
Date:	17-05-2022
Changes:	Sound Pressure Level Updated
Changes Made by:	Paul Doyle

Revision: C	
Date:	12-08-2022
Changes:	Cover updated Introduction updated Specifications updated Reliability test updated
Changes Made by:	Carlos Gomes

Changes:	Cover updated Introduction updated Specifications updated Reliability test updated Specifications updated
Changes Made by:	Carlos Gomes

www.taoglas.com SPE-22-8-010-D 10



www.taoglas.com

