# MBC275 Series

Ultra-Low Profile Open Frame Power Supplies Medical

Not For New Design Please refer to exact equivalent product series

**MULP275** 

The MBC275 Series of ultra low open frame medical power supplies feature a wide universal AC input range of 85 V – 264 VAC, offering 275 W of output power with forced air cooling in a variety of isolated single output voltages.

The MBC Series is designed and approved to the latest medical standards (EN/IEC 60601-1), providing 2 x MOPP isolation for Class I & Class II applications.

These power supplies are ideal for medical, telecom, datacom, industrial equipment and other applications.



- 5 x 3 x 0.75 Inches Form factor
- 275 Watts with Forced Air Cooling
- Approved to EN/IEC 60601-1
- Efficiencies up to 92%
- -40 to 70°C degree operating temperature
- Dual fusing
- 12 V / 0.5 A Fan Output
- Thermal Shut-Down feature
- 3.37 million Hours, Telcordia -SR332-issue 3 MTBF
- No Load Power < 0.5 W</li>
- Medical (BF) Safety Approvals

#### **Applications**

- Diagnostic
- Drug Pump
- Monitoring

- Dialysis
- Home Health Care
- Portable Equipment







<sup>\*</sup> Class II means without input Earth pin.

#### **MODEL SELECTION**

| MODEL NUMBER 1             | OUTPUT CONNECTOR            | VOLTAGE | CONVECTION 50°C<br>(152 W) | MAX. LOAD<br>CONVECTION 40°C<br>(160 W) | 13 CFM<br>(275 W) | POWER  |
|----------------------------|-----------------------------|---------|----------------------------|---|-------------------|--------|
| MBC275-1T12L               | Screw Terminal              | 12 V    | 12.5 A                     | 13.33 A                                 | 22.92 A           | 275 W  |
| MBC275-1012L               | Header Molex Connector      |         | 12.071                     | 10.0071                                 | 22.0271           | 210 ** |
| MBC275-1T15L               | Screw Terminal              | 15 V    | 10 A                       | 10.66 A                                 | 18.33 A           | 275 W  |
| MBC275-1015L               | Header Molex Connector      | 13 V    | 10 A                       | 10.00 A                                 | 10.55 A           | 213 W  |
| MBC275-1T24L               | Screw Terminal              | 24 V    | 6.25 A                     | 6.67 A                                  | 11.46 A           | 275 W  |
| MBC275-1024L               | Header Molex Connector      | Z4 V    | 0.23 A                     | 0.07 A                                  | 11.40 A           | 213 W  |
| MBC275-1T30L               | Screw Terminal              | 30 V    | 5 A                        | 5.33 A                                  | 9.17 A            | 275 W  |
| MBC275-1030L               | Header Molex Connector      | 30 V    | 5 A                        | 3.55 A                                  | 3.17 A            | 215 W  |
| MBC275-1T48L               | Screw Terminal              | 48 V    | 3.12 A                     | 3.33 A                                  | 5.73 A            | 275 W  |
| MBC275-1048L               | Header Molex Connector      | 70 V    | 3.12 A                     | 0.0071                                  | 0.107             | 210 W  |
| MBC275-1T58L               | Screw Terminal              | 58 V    | 2.58 A                     | 2.76 A                                  | 4.74 A            | 275 W  |
| MBC275-1058L               | Header Molex Connector      | 55 V    | 2.50 A                     | 2.101                                   | 7.7 TA            | 210 11 |
| COVER-275-XBC <sup>2</sup> | Metal Cover Kit (accessory) |         |                            |   |                   |        |

Class II version available. Add suffix "-2" at the end of the Model Number. Class II means without input Earth pin. When used in Cover Kit, de-rate output power to  $70\,\%$  under all operating conditions.

#### **INPUT SPECIFICATIONS** 2.

Specifications are for nominal input voltage, 25°C unless otherwise stated.

| PARAMETER           | DESCRIPTION / CONDITION  | SPECIFICATION               |
|---------------------|--|-----------------------------|
| Input Voltage       | Universal (Derate from 100% at 100 VAC to 72% for forced cooling and 69% for convection cooling at 80 VAC) | 80 – 264 VAC / 390 VDC      |
| Input Frequency     |  | 47 – 63 Hz                  |
| Input Current       | 115 VAC:<br>230 VAC:   | 2.6 A max.<br>1.3 A max.    |
| No Load Power       | Typical  | < 0.5 W                     |
| Inrush Current      | 115 VAC:<br>230 VAC:<br>264 VAC:   | 25 A<br>45 A<br>75 A        |
| Leakage Current     | Typical (N/A for Class II Option) Touch current  | 300 μA<br>< 100 μA          |
| Switching Frequency | PFC<br>PWM   | 70 – 130 kHz<br>50 – 80 kHz |



#### 3. OUTPUT SPECIFICATIONS

| PARAMETER                              | DESCRIPTION / CONDITION  | SPECIFICATION            |
|--|--|--------------------------|
| Output Voltage                         | Refer to Model selection table   | From 12 V to 58 V        |
| Output Power <sup>3</sup>              | 13 CFM (forced air cooling)<br>Convection (natural cooling)  | 275 W<br>up to 160 W     |
| Efficiency                             | 48 V, 58 V:<br>24 V, 30 V:<br>12 V, 15 V:  | 92%<br>90%<br>88%        |
| Hold-up Time                           | At 275 W:<br>At 160 W:   | 8 ms<br>16 ms            |
| Power Factor                           | @ Full Load  | > 0.95                   |
| Line Regulation <sup>4</sup>           |  | ± 0.5%                   |
| Load Regulation <sup>4</sup>           |  | ± 1%                     |
| Minimum Load                           |  | 0.0 A                    |
| Transient Response                     | 25% step load change, at 0.1 A/ μs slew rate,<br>50% duty cycle, 50 Hz = 4%  | recovery time < 5 ms     |
| Ripple <sup>4, 5</sup>                 | 24, 30, 48 & 58 V outputs<br>12 V & 15 V outputs   | 1.0 % max.<br>2.0 % max. |
| Output Voltage Adjustment <sup>6</sup> |  | ± 3%                     |
| Rise Time                              | Typical  | 55 ms                    |
| Set Point Tolerance 4                  |  | ± 1%                     |
| Over Current Protection                |  | > 110%                   |
| Over Voltage Protection                |  | 110 to 140%              |
| Short Circuit Protection               | Hiccup mode  |                          |
| Cooling                                | With 13 CFM forced air cooling (100 to 264 VAC) <sup>7</sup> With natural convection cooling (100 to 264 VAC) <sup>8</sup> | 275 W<br>Up to 160 W     |

- <sup>3</sup> Combined output power of main output, fan supply shall not exceed max. power rating.
- <sup>4</sup> Fan supply output voltage tolerance including set point accuracy, line and load regulation is ± 10% and ripple and noise is less than 10%.
- <sup>5</sup> Ripple is peak to peak with 20 MHz bandwidth and 10 μF (Electrolytic capacitor) in parallel with a 0.1 μF capacitor at rated line voltage and load ranges.
- <sup>6</sup> Adjustment potentiometer is located on the SMT side of the PCB
- Refer to Mechanical Drawing
- 8 Refer to Derating Curve

# 4. EMC SPECIFICATIONS

| PARAMETER                          | DESCRIPTION / CONDITION  | SPECIFICATION        |
|------------------------------------|--|----------------------|
| Conducted Emissions                | EN 55011-B, CISPR22-B, FCC PART15-B  | Pass                 |
| Radiated Emissions                 | EN 55011 A with external core (King core K5B RC 25x12x15-M in input cable) | Pass<br>Level B      |
| Input Current Harmonics            | EN 61000-3-2   | Class D              |
| Voltage Fluctuation and Flicker    | EN 61000-3-3   | Pass                 |
| ESD Immunity                       | EN 61000-4-2   | Level 4, Criterion A |
| Radiated Field Immunity            | EN 61000-4-3   | Level 3, Criterion A |
| Electrical Fast Transient Immunity | EN 61000-4-4   | Level 3, Criterion A |
| Surge Immunity                     | EN 61000-4-5   | Level 3, Criterion A |
| Conducted Immunity                 | EN 61000-4-6   | Level 3, Criterion A |
| Magnetic Field Immunity            | EN 61000-4-8   | Level 4, Criterion A |
| Voltage Dips, Interruptions        | EN 61000-4-11  | Criterion B          |



#### 5. SAFETY SPECIFICATIONS


| PARAMETER          | DESCRIPTION / CONDITION  | SPECIFICATION                               |
|--------------------|--|---|
| Isolation Voltage  | Input to Output: (Medical applications) Input to GND: (N/A for Class II Option) Output to GND: for type BF (for type B (N/A for Class II Option) | 4000 VAC<br>1500 VAC<br>1500 VAC<br>500 VAC |
| Safety Standard(s) | EN 60601-1, IEC 60601-1 (ed.3), ANSI / AAMI ES 60601 -   | I, CSA C22.2 No. 60601-1                    |
| Agency Approvals   | Nemko, UL, C-UL  |   |
| CE mark            | Complies with LVD Directive  |   |

### 6. ENVIRONMENTAL SPECIFICATIONS

| PARAMETER               | DESCRIPTION / CONDITION                            | SPECIFICATION            |
|-------------------------|--|--------------------------|
| Operating Temperature 9 | -40 to 0°C startup guaranteed, with spec deviation | -40 to +70°C             |
| Storage Temperature     |  | -40 to +85°C             |
| Relative Humidity       | Non-condensing                                     | 5% to 95%                |
| Altitude                | Operating:<br>Non-operating:                       | 16,000 ft.<br>40,000 ft. |
| MTBF                    | Telcordia -SR332-issue 3                           | 3.37 million hours       |

Output ripple can be more than 10% of the output voltage.

#### **DERATING CURVES**



Convection load: 160 W up to 40 °C De-rate between 40-50 °C @ 0.625% per °C De-rate above 50 °C @ 2.33% per °C

Forced air cooled load: 275 W up to 50°C De-rate above 50 °C @ 2.5% per °C




Figure 1. Derating Curves



#### 7. CONNECTOR & PIN DESCRIPTION

| CONNECTOR           | PIN | DESCRIPT                   | TION / CONDITION                    | MANUFACTURER / PN   |
|---------------------|-----|----------------------------|-------------------------------------|---|
| AC Input Connector  | J1  | Pin 1<br>Pin 2<br>Pin 3    | AC Line<br>Not Fitted<br>AC Neutral | Molex: 26-60-4030<br>Mating: 09-50-3031; Pins: 08-50-0106   |
| DC Output Connector | J2  | Pin 1, 2, 3<br>Pin 4. 5. 6 | V1 +VE<br>V1 -VE                    | Option 1 (Screw Terminal): Molex: 39357 Series or equivalent Option 2 (Molex Connector): Molex: 26-60-4060 Mating: 09-50-3061; Pins: 08-50-0106 |
| Aux (Fan) Output    | J3  | Pin 1<br>Pin 2             | FAN +VE<br>FAN -VE                  | AMP: 640456-2<br>Mating: 640440-2   |

#### 8. MECHANICAL SPECIFICATIONS

| PARAMETER  | DESCRIPTION / CONDITION                     |  |  |
|------------|---|--|--|
| Weight     | approx. 250 g                               |  |  |
| Dimensions | 127 x 76.2 x 19.05 mm (5 x 3 x 0.75 inches) |  |  |





Figure 2. Mechanical Drawing – Option 1 (Output Connector – Screw Terminal)

**NOTES:** In case the PCB is mounted in a metal enclosure, using metal hardware ensure the following:

- 1 Stand off, used to mount PCB has OD of 5.4 mm max.
- 2 Screws, used to fix PCB on stand off, have head dia of 6.0 mm max.
- 3 Washer, if used, to have dia of 6.5 mm max.





ALL DIMENSIONS ARE IN INCHES[MM] GEN TOLERANCE : +/-0.04[1.0MM]

Figure 3. Mechanical Drawing - Option 2 (Output Connector - Header Molex)

**NOTES:** In case the PCB is mounted in a metal enclosure, using metal hardware ensure the following:

- Stand off, used to mount PCB has OD of 5.4 mm max.
- 5 Screws, used to fix PCB on stand off, have head dia of 6.0 mm max.
- 6 Washer, if used, to have dia of 6.5 mm max.






Figure 4. Mechanical Drawing - Cover Kit Option

# For more information on these products consult: tech.support@psbel.com

**NUCLEAR AND MEDICAL APPLICATIONS** - Products are not designed or intended for use as critical components in life support systems, equipment used in hazardous environments, or nuclear control systems.

**TECHNICAL REVISIONS** - The appearance of products, including safety agency certifications pictured on labels, may change depending on the date manufactured. Specifications are subject to change without notice.



**Asia-Pacific** +86 755 298 85888 Europe, Middle East +353 61 49 8941 North America +1 866 513 2839