SIEMENS

Data sheet

US2:22LPU32BL



Reversing motor starter, Size 5, Three phase full voltage, Solid-state overload relay, OLR amp range 55-250A, 240-277V 50-60Hz/DC coil, Non-combination type, Enclosure type 1, Indoor general purpose use, Standard width enclosure

Figure similar

product brand name	Class 22
design of the product	Full-voltage reversing motor starter
General technical data	
weight [lb]	134 lb
Height x Width x Depth [in]	40 × 20 × 11 in
touch protection against electrical shock	NA for enclosed products
installation altitude [ft] at height above sea level maximum	6560 ft
ambient temperature [°F]	
 during storage 	-22 +149 °F
during operation	-4 +104 °F
ambient temperature	
 during storage 	-30 +65 °C
during operation	-20 +40 °C
country of origin	USA
Horsepower ratings	
yielded mechanical performance [hp] for 3-phase AC motor	
 at 200/208 V rated value 	75 hp
 at 220/230 V rated value 	100 hp
 at 460/480 V rated value 	200 hp
 at 575/600 V rated value 	200 hp
Contactor	
size of contactor	NEMA controller size 5
number of NO contacts for main contacts	3
operating voltage for main current circuit at AC at 60 Hz maximum	600 V
operational current at AC at 600 V rated value	270 A
mechanical service life (switching cycles) of the main contacts typical	1000000
Auxiliary contact	
number of NC contacts at contactor for auxiliary contacts	2
number of NO contacts at contactor for auxiliary contacts	2
number of total auxiliary contacts maximum	8
contact rating of auxiliary contacts of contactor according to UL	10A@240VAC (A300), 2.5A@250VDC (Q300)
Coil	
type of voltage of the control supply voltage	AC/DC
control supply voltage	
• at DC rated value	240 277 V

	040 077 \/
at AC at 50 Hz rated value	240 277 V
at AC at 60 Hz rated value	240 277 V 7.4 W
holding power at AC minimum	590 VA
apparent pick-up power of magnet coil at AC	6.7 VA
apparent holding power of magnet coil at AC operating range factor control supply voltage rated value	0.85 1.1
of magnet coil	
percental drop-out voltage of magnet coil related to the input voltage	60 %
ON-delay time	30 95 ms
OFF-delay time	40 80 ms
Overload relay	
product function	
 overload protection 	Yes
 phase failure detection 	Yes
 asymmetry detection 	Yes
 ground fault detection 	No
test function	Yes
external reset	Yes
reset function	Manual and automatic
trip class	CLASS 20
adjustable current response value current of the current- dependent overload release	55 250 A
product feature protective coating on printed-circuit board	No
number of NC contacts of auxiliary contacts of overload relay	1
number of NO contacts of auxiliary contacts of overload relay	1
operational current of auxiliary contacts of overload relay	
• at AC at 600 V	5 A
• at DC at 250 V	1 A
contact rating of auxiliary contacts of overload relay according to UL	5A@600VAC (B600), 1A@250VDC (R300)
insulation voltage (Ui)	
 with single-phase operation at AC rated value 	600 V
 with multi-phase operation at AC rated value 	300 V
Enclosure	
degree of protection NEMA rating	1
design of the housing	indoors, usable on a general basis
Mounting/wiring	
mounting position	Vertical
fastening method	Surface mounting and installation
type of electrical connection for supply voltage line-side	Box lug
tightening torque [lbf·in] for supply	180 195 lbf·in
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	3/0 AWG 600 MCM (front only) or 250 500 MCM (back only) or 2x 2/0 AWG 2x 500 MCM (both front & back)
temperature of the conductor for supply maximum permissible	75 °C
type of electrical connection for load-side outgoing feeder	Box lug
tightening torque [lbf·in] for load-side outgoing feeder	180 220 lbf·in
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded	2x 2/0 AWG 500 MCM
temperature of the conductor for load-side outgoing feeder maximum permissible	75 °C
material of the conductor for load-side outgoing feeder	CU
type of electrical connection of magnet coil	Screw-type terminals
tightening torque [lbf·in] at magnet coil	7 10 lbf in
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (18 14 AWG)
temperature of the conductor at magnet coil maximum permissible	75 °C
material of the conductor at magnet coil	CU

type of electrical connection for auxiliary contacts	Screw-type terminals	
tightening torque [lbf·in] at contactor for auxiliary contacts	7 10 lbf·in	
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	2x (20 16 AWG), 2x (18 14 AWG)	
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C	
material of the conductor at contactor for auxiliary contacts	CU	
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals	
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in	
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 14 AWG)	
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C	
material of the conductor at overload relay for auxiliary contacts	CU	
Short-circuit current rating		
design of the fuse link for short-circuit protection of the main circuit required	14kA@600V (Class H or K); 100kA@600V (Class R or J)	
design of the short-circuit trip	Thermal magnetic circuit breaker	
breaking capacity maximum short-circuit current (Icu)		
• at 240 V	14 kA	
• at 480 V	14 kA	
• at 600 V	14 kA	
certificate of suitability	NEMA ICS 2; UL 508	
Further information		
Industrial Controls - Broduct Overview (Catalogs, Brook		

Industrial Controls - Product Overview (Catalogs, Brochures,...)

www.usa.siemens.com/iccatalog

Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:22LPU32BL


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/US/en/ps/US2:22LPU32BL

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:22LPU32BL&lang=en

Certificates/approvals

https://support.industry.siemens.com/cs/US/en/ps/US2:22LPU32BL/certificate



LETTER	CONDUIT SIZE
	ø12.7 & ø19 CONDUIT
B	ø31.8 & ø38.1 CONDUIT
С	ø50.8 & ø76.2 CONDUIT

last modified:

1/25/2022 🖸