

11

6

5 (4+PE)

power

6000[°]V

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

zinc diecast / chromated

PA 6.6 mod., UL 94/V0

500

3

ĪII

FKM

2000 m

-20 °C to 130 °C

when connected IP 66/67

max. 30 A* max. 1.2 A* 850V/DC 630V/AC 50V/DC 30V/AC

signal

1500 V

Technical Data

number of pins

rated current rated voltage

mating cycles

pollution dearee

Material

insulation insert

housing

seals

over voltage category

max. height for operation

Contacts (not part of product contents)

Tools (not part of product contents)

temperature range protection type

Electrical Data

rated insulation voltage (L-L)

power signal

723 htec Receptacle

soeedtec

11-pin insulation insert Code 1 male Earth-to-Housing Connection according to VDE 0627 Protection Against Contact according to VDE 0623 Electrically Protective Separation according to VDE 0140 flange mount /Flange 25x25

H 53 C 011 NN 00 00 0200 000 H E C 011 N 00 00 0200 000



Contact Arrangement

mating view


© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without paties. Consult TE for the notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mail: intercontec@te.com Web: www.intercontec.biz





Main Dimensions Receptacle

*for max, wire cross-section pay attention to the cross-section of used contacts

œ 03.09.201 ssue: