


ED350V-XXP

PCB Terminal Blocks > PCB Terminal Blocks

Date:2021-05-19Version:V1





The web catalog is for reference only. Dinkle remains the right of product modification and engineering change of the design.

The final product is made according to engineering drawing.

Product Description

Pitch: 3.50mm, 300V, 10A

General information

Short description	PCB Terminal Blocks , Wire Protector Type
Category	PCB Terminal Blocks
Pitch (mm)	3.5
Color	Green(default)
Connection method	Wire Protector Type
Type of locking	Without
Length (mm)	3.50xP
Width (mm)	6.8
Height (mm)	8.4
Pin demensions (Thickness x Width)(mm)	Ø0.77
PCB hole diameter (mm)	1.0~1.2
Number of positions	02~21
Level	Single level

Material information

Insulation material	PA
---------------------	----



Insulation material group	I
Flame retardant rating , compliant with UL94	VO
Conductor material	Copper Alloy
Plating of conductor surface	Tinned
Connection data-IEC	
Rated voltage (V)	130
Rated current (A)	10
Rated voltage (II/2)(V)	320
Rated voltage (III/2) (V)	160
Rated voltage (III/3)(V)	160
Rated impulse voltage (II/2)(KV)	2.5
Rated impulse voltage (III/2)(KV)	2.5
Rated impulse voltage (III/3)(KV)	2.5
Conductor cross section solid. min (mm²)	0.5
Conductor cross section solid.max (mm²)	1.5
Conductor cross section stranded. min (mm²)	0.5
Conductor cross section stranded. max (mm²)	1.5
Conductor cross section flexible, with min ferrule without plastic sleeve (mm²)	0.25
Conductor cross section flexible, with max ferrule without plastic sleeve (mm²)	1.5
Conductor cross section flexible, with min ferrule with plastic sleeve (mm²)	0.25
Conductor cross section flexible, with max ferrule with plastic sleeve (mm²)	1.5
2 conductors with same cross section, solid, max (mm²)	0.75
2 conductors with same cross section, stranded, max (mm²)	0.75
Screw thread	M2
Rated torque (N.m)	0.2
Stripping Length (mm)	5~6
Connection data-UL	
Rated voltage (UL/CUL Group B)(V)	300
Rated current (UL/CUL Group B)(A)	10
Min. solid wire connection (AWG) acc. to UL/CUL	24

Max. solid wire connection AWG acc. to UL/CUL	16
Min. stranded wire connection AWG acc. to UL/CUL	24
Max. stranded wire connection AWG acc. to UL/CUL	18

Environment & Safety

Finger protection (YES or NO)	YES
Operating temperature. max (°C)	115
Operating temperature. min (°C)	-40

UL Recognized

Wire Range (Group B)(AWG)	24~16
Rated voltage (Group B)(V)	300
Rated current (Group B)(A)	10


CUL Recognized


Wire Range (Group B)(AWG)	24~16
Rated voltage (Group B)(V)	300
Rated current (Group B)(A)	10

VDE Approval

Wire Range (mm²)	0.5~1.5
Rated voltage (V)	130
Rated current (A)	10

Drawings







Approvals





