




**QMQF326** and **QVMQF326** are QuikXO™ (quick-turn delivery) versions of the MQF326 (a TCXO) and VMQF326 (a VCTCXO) series, respectively. QuikXO™ products, either standard or custom frequencies are produced and shipped from California USA in 3 to 5 days and available at Mercury eCommerce. They are 3.2 x 2.5 x 1.6 mm miniature SMD, the supply voltage can be either 2.5 V or 3.3 V and output logics include CMOS (up to 250 MHz), differential LVPECL or LVDS (up to 1.5 GHz). The 0.8 ~ 1.6 ps typical phase jitter and lower current consumption (43 mA typical for LVPECL 622.080 MHz at 3.3 V) compared to competitions make the series ideal for multimedia, Ethernet, and networking applications.



**Relevant Categories:**

- For lower cost with regular lead time, please refer to the non- QuikXO™ equivalent, the **MQF326**, and the **VMQF326** series.
- For lower phase noise and phase jitter (0.6 p. sec. typical), please refer to the **MQN326** and **VMQN326** series.
- For 7.0 x 5.0 x 2.5 mm with the same electrical performance, please refer to the **QMQF574**, **QVMQF574** (CMOS; 4-pad), and **QMQF576**, **QVMQF576** (LVPECL or LVDS; 6-pad) series.

**General Specifications:** at Ta= +25°C

Output Logic Type	CMOS (code "T")		LVPECL (code "P")		LVDS (code "D")	
	QMQF326T25	QMQF326T33	QMQF326P25	QMQF326P33	QMQF326D25	QMQF326D33
TCXO Models	QMQF326T25	QMQF326T33	QMQF326P25	QMQF326P33	QMQF326D25	QMQF326D33
VCTCXO Models	QVMQF326T25	QVMQF326T33	QVMQF326P25	QVMQF326P33	QVMQF326D25	QVMQF326D33
Frequency Range	10 ~ 250 MHz		10 ~ 1500 MHz		10 ~ 1500 MHz	
Supply Voltage (V <sub>DD</sub> )	+2.5 V ±5%	+3.3 V ±5%	+2.5 V ±5%	+3.3 V ±5%	+2.5 V ±5%	+3.3 V ±5%
	Code "25"	Code "33"	Code "25"	Code "33"	Code "25"	Code "33"
Current Consumption (mA; typical)	25 MHz: 17	10 MHz: 21	18 MHz: 28	18 MHz: 35	11 MHz: 19	11 MHz: 22
	45 MHz: 20	50 MHz: 24	156 MHz: 30	156 MHz: 38	190 MHz: 23	155.5 MHz: 26
	50 MHz: 21	77 MHz: 25	622 MHz: 33	622 MHz: 43	390 MHz: 24	250 MHz: 28
	125 MHz: 24	125 MHz: 29	1289 MHz: 37	1289 MHz: 51	1289 MHz: 31	1080 MHz: 32
	250 MHz: 25	250 MHz: 34	1500 MHz: 43	1500 MHz: 52	1500 MHz: 34	1500 MHz: 35
Load; typical	15 pF		50 Ω into V <sub>CC</sub> - 2.0 V or Thevenin equivalent		100 Ω across the outputs	
Output "High" Voltage; (V <sub>OH</sub> )	90% V <sub>DD</sub> min.		V <sub>DD</sub> -1.03 V min.; V <sub>DD</sub> -0.6 V max.		1.4 V typical; 1.6 V max.	
Output "Low" Voltage; V <sub>OL</sub>	10% V <sub>DD</sub> max.		V <sub>DD</sub> -1.85 V min.; V <sub>DD</sub> -1.6 V max		1.1 V typical; 0.9 V min.	
Rise Time (Tr) / Fall Time (Tf)	1.5 nS. Typ.; 3.0 nS. max. (10% ↔ 90% waveform)		0.2 nS Typ.; 0.5 nS max. (20% ↔ 80% waveform)		0.2 nS Typ.; 0.4 nS max. (20% ↔ 80% waveform)	



<b>Additional Output AC Characteristics for LVDS output (LVDS only)</b>	Differential Output Voltage ( $V_{OD}$ ): 175 mV min.; 350 mV typical $V_{OD}$ Magnitude Change ( $\Delta V_{OD}$ ): 50 mV max. Offset Voltage ( $V_{OS}$ ): 1.25 V typical $V_{OS}$ Magnitude Change ( $\Delta V_{OS}$ ): 50 mV max.												
<b>Frequency Stability vs</b>	Operating Temperature	$\pm 2.0$ ppm over -40 to +85°C. Spec. code: "2.0A".											
		$\pm 2.5$ ppm over -30 to +85°C. Spec. code: "2.5B".											
		Custom specification: The 2.0A or 2.5B is replaced with a control number assigned by Mercury.											
	Voltage Change	$\pm 0.2$ ppm max. for a $\pm 5\%$ input voltage change											
	Load Change	$\pm 0.2$ ppm max. for a $\pm 10\%$ load condition change											
	Aging at $T_a = +25^\circ\text{C}$	$\pm 2$ ppm max. first-year; $\pm 10$ ppm max. over 10 years											
Reflow	$\pm 1.0$ ppm max., one reflow and measured 24 hours afterward.												
<b>Initial Calibration Tolerance (Initial Frequency Accuracy)</b>	$\pm 1.0$ ppm typical; $\pm 2.0$ ppm. max. at $+25^\circ\text{C} \pm 2^\circ\text{C}$ .												
<b>Duty Cycle</b>	50% $\pm 5\%$ . At 50% $V_{DD}$ .												
<b>Current with Output Disabled</b>	18 mA typical												
<b>Start-up Time</b>	5 m. sec. max.												
<b>Output Enable Time</b>	200 ns max.												
<b>Output Disable Time</b>	50 ns max.												
<b>Single Side-band Phase Noise (dBc/Hz; typical)</b>	Frequency (MHz)	16	25	49.152	50	54	156.250	600	1030	1080	1270	1450	
	Supply Voltage	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	
	Output Logic	T	T	T	T	T	P	P	P	D	D	D	
	Offset	10 Hz	-92	-88	-85	-80	-77	-63	-59	-53	-49	-49	-52
		100 Hz	-116	-109	-108	-103	-106	-91	-81	-75	-81	-78	-78
		1 kHz	-131	-125	-121	-117	-119	-109	-96	-93	-93	-91	-89
		10 kHz	-139	-132	-126	-124	-125	-115	-102	-94	-98	-94	-92
		100 kHz	-140	-134	-127	-127	-126	-116	-104	-97	-99	-97	-94
		1 MHz	-158	-151	-146	-145	-145	-137	-125	-119	-120	-117	-118
		5 MHz	-163	-157	-154	-148	-153	-147	-132	-129	-128	-128	-129
10 MHz		-	-	-157	-150	-157	-150	-136	-133	-133	-133	-133	
20 MHz	-	-	-160	-152	-160	-155	-139	-	-142	-142	-		
<b>Integrated Phase Jitter, RMS 12 kHz to 20 MHz, picosecond</b>	0.76	0.9	1.0	1.1	1.1	1.1	1.1	1.4	1.1	1.2	1.4		
<b>Control Voltage Function on Pad 1 (VCTCXOs only)</b>													
<b>Control Voltage (<math>V_{control}</math>)</b>	$V_{control}$ center and range: $+1.5\text{ V} \pm 1.0\text{ V}$ . For both 2.5 $V_{DD}$ and 3.3 $V_{DD}$												
<b>Frequency Pulling Range</b>	High pull: +8 ppm min. for $V_{control}$ from 1.5 V to +2.5V Low pull: -8 ppm min. for $V_{control}$ from 0.5 V to +1.5V												
<b>Linearity</b>	$\pm 5\%$ typical. $\pm 10\%$ max.												
<b>Transfer Function</b>	Positive Transfer												
<b>Input Impedance</b>	500 K $\Omega$ min.												
<b>Bandwidth</b>	10 kHz min. Measured at -3 dB.												

Tri-State function on Pad 2	
Output Enable (OE) Control	70% of V <sub>DD</sub> (min.) to enable output. CMOS level. Do not leave this pin floating. If no connection is desired, please contact Mercury.
	30% of V <sub>DD</sub> (max.) to disable the output. Output is high impedance.
Output Enable Time	200 n. sec. max.
Output Disable Time	50 n. sec. max.

### Absolute Maximum Rating:

Input Voltage	-0.5 V to V <sub>DD</sub> +0.5 V
Output Voltage	-0.5 V to V <sub>DD</sub> +0.5 V
Positive Supply Voltage	4.2 V
Electrostatic Discharge (ESD)	Human Body Model (HBM): Exceeds 2000 V. Class 2 per MIL-STD-1686C
	Machine Model (MM): Exceeds 120 V. Class M2 per MIL-STD-1686C. Note: Power, ground, and outputs are 200 V.
	Charged-Device Model (CDM): Exceeds 2000 V. Class C6 per MIL-STD-1686C

### Environmental Performance Specifications

Green Requirement	RoHS compliant, Pb (lead) free per EU Directive 2002/95/EC 6/6 (2002/95/EC) and WEEE (2002/96/EC). Free of halide, cadmium, hexavalent chromium, lead, mercury, PBBs, and PBDEs.
Moisture Sensitivity Level	Level 2 per IPC/JEDEC J-STD-020D.1
Storage temperature range	-55 to +125°C
Humidity	85% RH, 85°C, 48 hours
Fine Leak / Gross Leak	MIL-Std-883, method 1014, condition A / MIL-Std-883, method 1014, condition C
Solderability	MIL-STD-202F method 208E
Reflow	260°C for 10 sec. 2X.
Vibration	MIL-STD-202F method 204, 35G, 50 to 2000 Hz
Shock	MIL-STD-202F method 213B, test condition. E, 1000GG ½ sine wave
Resistance to Solvent	MIL-STD-202, method 215
Temperature Cycling	MIL-STD-883, method 1010
Pad Surface Finish	Gold (0.3 um to 1.0 um) over nickel (1.27 um to 8.89 um)

### Part Number Format and Examples:


Example 1: QVMQF326D33-2.0A-622.080;

Example 2: QMQF326T25-2.5B-148.500;


Example 3: QMQF326P33-xxxx-155.520

QVMQF	326	D	33	-	2.0A	-	622.080
QMQF	326	T	25	-	2.5B	-	148.500
QMQF	326	P	33	-	xxxx	-	155.520
Product Series "QMQF": TCXO "QVMQF": VCTCXO	Package Code "326": 3.2x2.5 mm 6-pad SMD	Output Logic "T": CMOS "P": LVPECL "D": LVDS	Supply Voltage "33" for 3.3V "25" for 2.5V	-	"2.5B": The freq. stability is ±2.5 ppm over -30 to +85°C "2.0A": The freq. stability is ±2.0 ppm over -40 to +85°C "xxxx": Custom frequency stability. A control number assigned by Mercury.	-	The nominal Frequency in MHz. 3 places or more after the decimal.

**Output OE Function on pad 2** Note: Do not leave this pad floating. If “no-connection” is desired, please contact Mercury.




**Phase Noise Plot of QMQF326T33-89.376 MHz,  $V_{DD} = +3.3V$ , CMOS**




**Package Dimensions and Recommended Solder Pad Layout**

unit: (mm)





**Test Circuits and Output Waveforms**


Duty cycle =  $\left(\frac{T_1}{T_2}\right) * 100\%$ . Measured at 50% V<sub>DD</sub>



### LVDS



### Recommended Solder Reflow Profile (per IPC/JEDEC J-STD-020D.1)



Profile Feature	Sn-Pb Eutectic Assembly	Pb-free Assembly
Preheat/Soak		
- Temperature min. (Ts min.)	100°C	150°C
- Temperature max. (Ts max.)	150°C	200°C
- Time (ts) (Ts min. to Ts max.)	60 to 120 seconds	60 to 180 seconds
Ramp-up rate (TL to Tp)	3°C / sec. max.	3°C / sec. max.
Liquidous temperature (TL)	183°C	217°C
Time (tL) maintained above TL	60 to 150 seconds	60 to 150 seconds
Peak package body temperature (Tp)	235°C	260°C
Time (Tp) within 5°C of the classification temperature Tc	10 to 30 seconds	20 to 40 seconds
Ramp-down rate (Tp to TL)	6°C / second max.	6°C / second max.
Time 25°C to peak temperature	6 minutes max.	8 minutes max.

All temperatures refer to the topside of the package, measured on the package body surface.