
RoHS COMPLIANT



Electrical Characteristics

Nominal Impedance: 60-75 Ohms Frequency Range: DC to 900 MHz Operating Voltage (DC): 4000 V maximum

Dielectric Withstand Voltage (rms): 1500 V maximum at sea level Contact Resistance: 3.0 milliohms maximum Insulation Resistance: 10000 megohms minimum

Mechanical Characteristics

500 cycles minimum Mating Cycles:

Environmental Characteristics

Temperature Range: -55 °C to +85 °C

	PART	DESCRIPTION
1	Spring	Steel, Tin Plated
2	Body	Steel, Tin Plated
3	Insulator	Glass Fibre
4	Contact	Brass, Tin plated

First Issue	PDC	1	06 Sep 02
DESCRIPTION OF REVISION	APPVD	ISS	DATE



Cinch Connectivity Solutions 7-13 Russell Way, Widford Industrial Estate, Chelmsford, Essex, CM1 3AA, UK. Tel: +44 (0) 1245 359515

Fax: +44 (0) 1245 358938

P D Couzens DRAWN BY: SCALE: Not To Scale DIMENSIONS: mm CHECKED BY: S Nash TOLERANCES: APPROVED BY: G Dalton ± 0.2mm unless otherwise stated DATE 06 Sep 02

TITLE:

Euro PCB Mount Jack

PART NUMBER:

VEU334

PAGE: 1 of 1