






COAXIAL TERMINATION N MALE 2 GHZ 12W

PAGE 1/2 ISSUE 06-07-18A SERIES PART NUMBER R404557000 TERMINATION







All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)
Body	BRASS	NICKEL 5
Center contact	BRASS	GOLD 2.5 OVER NICKEL 1
Outer contact	BRASS	NICKEL 5
Insulator	PTFE	
Gasket	SILICONE RUBBER	
Substrate	ALUMINA	
Resistor	THICK FILM	
Others parts	ALUMINIUM	BLACK ANODIZATION





COAXIAL TERMINATION N MALE 2 GHZ 12W

PAGE 2/2	ISSUE 06-07-18A	SERIES	PART NUMBER R404557000
		TERMINATION	

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 2
V.S.W.R (≤)	1.10

Operating Frequency Range	DC - 2	GHz
Impedance	50	Ω
DC Resistance	50	Ω ± 5%
Peak power at 25°C (1µs, 1‰)	4000	W
Average power at 25°C	12	W (Free Air Cooled)
		W (Conduction Cooled)
		W (Conduction Co


MECHANICAL CHARACTERISTICS

Connectors	N	MALE	MIL C 39012
Weight	82,6300 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55 /+125	°C
Storage temperature range	-55 /+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS