




COAXIAL TERMINATION SMA FEMALE 6 GHZ 100W







COAXIAL TERMINATION SMA FEMALE 6 GHZ 100W

PAGE <b>2/2</b>	ISSUE 08-11-19B	SERIES TERMINATION	PART NUMBER <b>R404775000</b>
-----------------	-----------------	-----------------------	-------------------------------

## **ELECTRICAL CHARACTERISTICS**

Frequency (GHz)	DC - 3	3 - 6
V.S.W.R (≤)	1.20	1.40

Operating Frequency Range	DC - 6	GHz
Impedance	50	Ω
DC Resistance	50	Ω ± 5%
Peak power at 25°C (1µs, 1‰)	2000	W
Average power at 25°C	100	W (Free Air Cooled)
		W (Conduction Cooled)


### **MECHANICAL CHARACTERISTICS**

Connectors	SMA	Female	MIL C39012
Weight	<b>1 226,0000</b> g		

#### **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C

# Power derating Versus temperature



### SPECIFICATION

### **OTHER CHARACTERISTICS**

### MOUNTED WITH VERTICAL COOLING FINS AND NATURAL CONVECTION