

30 dB Fixed Attenuator, N Male to N Female Directional Black Anodized Aluminum Heatsink Body Rated to 150 Watts Up to 8 GHz



RF Fixed Attenuators Technical Data Sheet

PE7AP150-30

Features

- Directional
- DC to 8 GHz Frequency Range
- Attenuation 30±2 dB

- Max Power 150 Watts (CW)
- VSWR < 1.5:1

Applications

- Instrumentation
- · Precision measurements
- Prototyping and characterization
- · Production systems

Description

Pasternack carries a wide range of fixed attenuators with a broad selection of attenuation levels, frequency ranges, and power dissipation ranges. RF microwave attenuators (also known as RF pads) lower the amplitude of a signal (attenuate) a known amount and can be used in a wide variety of applications. These attenuator pads are used when a signal needs to be reduced to protect measurement equipment or other circuitry, to extend the range of power meters and amplifiers, and to impedance match circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and Pasternack carries one of the largest in-stock varieties and ships them same day. The 30 dB Fixed Attenuator PE7AP150-30 is rated to 150 Watts and operates from DC to 8 GHz. The versatile coaxial package uses type N male to type N female connectors and is also REACH and RoHS compliant. The Black Anodized Aluminum Heatsink body allows for efficient heat dissipation under high power usage conditions.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		8	GHz
Impedance		50		Ohms
Nominal Attenuation		30		dB
VSWR			1.5:1	
Input Power, CW			150	Watts
derated linearly to 15W at +125°C				
Input Power, Peak			2.5	kWatts
5µs pulse, 0.1% duty cycle				

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 30 dB Fixed Attenuator, N Male to N Female Directional Black Anodized Aluminum Heatsink Body Rated to 150 Watts Up to 8 GHz PE7AP150-30

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



30 dB Fixed Attenuator, N Male to N Female Directional Black Anodized Aluminum Heatsink Body Rated to 150 Watts Up to 8 GHz



RF Fixed Attenuators Technical Data Sheet

PE7AP150-30

Specifications by Frequency

Units	F5	F4	F3	F2	F1	Description
GHz		6 to 8	4 to 6	2 to 4	DC to 2	Range
		1.5:1	1.4:1	1.3:1	1.2:1	VSWR, Max
dB		2	1.5	1	0.75	Attenuation Accuracy, Typ
_		2		1.3:1		Attenuation Accuracy, Typ

Mechanical Specifications

Size

Length Width/Diameter

Height

Weight Body Material and Plating

6.39 in [162.31 mm] 5.8 in [147.32 mm] 4.21 in [106.93 mm] 4.598 lbs [2.09 Kg]

Black Anodized Aluminum Heatsink

Configuration Design

Fixed. Directional Package Style Connectorized Module

Connectors

Description	Connector 1	Connector 2	
Туре	N Male	N Female	
Connector Specification	MIL-STD-348	MIL-STD-348	
Contact Material and Plating	Beryllium Copper, Silver	Beryllium Copper, Silver	
Body Material and Plating	Stainless Steel, Silver	Stainless Steel, Silver	

Mechanical Specification Notes:

Connector interface in accordance with MIL-STD-348 and MIL-PRF-39012

Environmental Specifications

Temperature

-55 to +125 deg C Operating Range

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 30 dB Fixed Attenuator, N Male to N Female Directional Black Anodized Aluminum Heatsink Body Rated to 150 Watts Up to 8 GHz PE7AP150-30

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



30 dB Fixed Attenuator, N Male to N Female Directional Black Anodized Aluminum Heatsink Body Rated to 150 Watts Up to 8 GHz



RF Fixed Attenuators Technical Data Sheet

PE7AP150-30

30 dB Fixed Attenuator, N Male to N Female Directional Black Anodized Aluminum Heatsink Body Rated to 150 Watts Up to 8 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 30 dB Fixed Attenuator, N Male to N Female Directional Black Anodized Aluminum Heatsink Body Rated to 150 Watts Up to 8 GHz PE7AP150-30

URL: https://www.pasternack.com/30db-fixed-n-male-n-female-150-watts-attenuator-pe7ap150-30-p.aspx

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE7AP150-30 CAD Drawing

30 dB Fixed Attenuator, N Male to N Female Directional Black Anodized Aluminum Heatsink Body Rated to 150 Watts Up to 8 GHz

