





SMA ATTENUATOR 20 DB 12.4 GHZ 2W

PAGE 1/2 ISSUE 26-08-15E SERIES ATTENUATOR PART NUMBER R411820119







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body Male center contact	STAINLESS STEEL BERYLLIUM COPPER	PASSIVATED GOLD 2 OVER NICKEL 2
Female center contact	BERYLLIUM COPPER	GOLD 1.3 OVER NICKEL2
Outer contact	-	-
Insulator	PTFE	
Gasket	SILICONE RUBBER	
Substrate	ALUMINA	
Resistor	THIN FILM	
Others parts	-	-



Technical Data Sheet

SMA ATTENUATOR 20 DB 12.4 GHZ 2W

PAGE 2/2	ISSUE 26-08-15E	SERIES ATTENUATOR	PART NUMBER R411820119

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 4	4 - 8	8 - 12.4
V.S.W.R (≤)	1.20	1.25	1.30
Deviation(±dB)	0.50	0.60	0.50

Operating Frequency Range	DC - 12.4	GHz
Impedance	50	Ω
Nominal Attenuation	20	dB
Peak power at 25°C (1µs, 1‰)	100	W
Average power at 25°C	2	W (Free Air Cooled)
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	SMA	Male Female	MIL-C 39012
Weight	4,7300 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55 /+125 °C
Storage temperature range	-55/ +125 °C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS