





COAXIAL ATTENUATOR SMA 2.9 DC-40GHZ 2W - 6DB


PAGE 1/2 ISSUE 12-02-19C SERIES PART NUMBER R413306000 ATTENUATOR





Scale 1:1

All dimensions are in mm. Tolerances according ISO 2768 m-H





COMPONENTS	MATERIALS	PLATING (μm)
Body	STAINLESS STEEL	PASSIVATED
Male center contact	BERYLLIUM COPPER	GOLD 1.3 OVER NICKEL2
Female center contact	BERYLLIUM COPPER	GOLD 1.3 OVER NICKEL2
Outer contact	STAINLESS STEEL	PASSIVATED
Insulator		
Gasket	SILICONE RUBBER	
Substrate	ALUMINA CERAMIC	
Resistor	-	
Others parts	-	





COAXIAL ATTENUATOR SMA 2.9 DC-40GHZ 2W - 6DB

PAGE 2/2	ISSUE 12-02-19C	SERIES ATTENUATOR	PART NUMBER R413306000
-----------------	------------------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 40
V.S.W.R (≤)	1.60 (1.4 typ.)
Deviation(±dB)	0.8


Operating Frequency Range	DC - 40	GHz
Impedance	50	Ω
Nominal Attenuation	6	dB
Peak power at 25°C (1µs, 1‰)	100	W
Average power at 25°C	2	W (Free Air Cooled)
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

	Connectors	SMA 2.9	Male Female	MIL-C 39012
Г	Weight	6,5800	g	

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C





SPECIFICATION

OTHER CHARACTERISTICS

Temperature sensitivity: 4 * 10⁻⁴ dB / dB * °C