





TNC ATTENUATOR 6 DB 2 GHZ 80/100W

PAGE 1/2	ISSUE 17-08-18B	SERIES ATTENUATOR	PART NUMBER R417906128
-----------------	------------------------	----------------------	-------------------------------





All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS MATERIALS		PLATING (μm)	
Body Male center contact	STAINLESS STEEL BERYLLIUM COPPER	PASSIVATED GOLD 0.5 OVER NICKEL PHOSPHORUS 2	
Female center contact Outer contact Insulator	BERYLLIUM COPPER PTFE	GOLD 0.5 OVER NICKEL PHOSPHORUS 2	
Gasket	SILICONE RUBBER		
Substrate Resistor	ALUMINA THICK FILM		
Others parts	ALUMINIUM	BLACK PAINTING	



Technical Data Sheet

TNC ATTENUATOR 6 DB 2 GHZ 80/100W

PAGE 2/2	ISSUE 17-08-18B	SERIES ATTENUATOR	PART NUMBER R417906128
-----------------	-----------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 1	1 - 2
V.S.W.R (≤)	1.10	1.25
Deviation(±dB)	1.0	1.0

Operating Frequency Range	DC - 2	GHz
Impedance	50	Ω
Nominal Attenuation 6		dB
Peak power at 25°C (1µs, 1‰)	5000	W
Average power at 25°C	80	W (Free Air Cooled)
	100	W (Conduction Cooled)
For conduction cooling, a plate 1000 cm2 x 3 mm/156 sq.in*1/8) min, is required		


MECHANICAL CHARACTERISTICS

	Connectors	TNC	Male Female	MIL-C 39012
Weight 603,7000 g				

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55 /+125 °C
Storage temperature range	-55 /+125 °C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS