

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO RF INDUSTRIES, ANY UNAUTHORIZED USE OF THIS DRAWING IS EXPRESSLY PROHIBITED WITHOUT WRITTEN PERMISSION FROM RF INDUSTRIES.

ANY VIOLATION IS PUNISHABLE UNDER U.S. COPYRIGHT LAWS.

ALL DIMENSIONS ARE REFERENCE ONLY

PAR	RFB-1716-I-03			
REV	DESCRIPTION	DWN	DATE	APPROVED
_	ENGINEERING RELEASE	CZS	4/29/03	JDMc





MAX. PANEL THICKNESS: .157"

SPECIFICATIONS:

IMPEDANCE: 75 Ohms

FREQUENCY RANGE: 0-4 GHz

WORKING VOLTAGE: 500 V rms @ sea level TEMPERATURE RANGE: -65°C TO 165°C INSULATION RESISTANCE: 5k M Ohms min.

	BODY			NICKEL, 100μ"	008974				7610 MIRAMAR RD
	INSULATOR CONTACT		PTFE PHOS. BRONZE	GOLD, 3μ"					- SAN DIFGO CA 92126
	INSULATOR		DELRIN						(858) 549-6340 (858) 549-6345 FA)
5	HOUSING	1	BRASS	NICKEL, 100 μ"					DIVISION OF RF INDUSTRIES, LTD. (838) 549-6345 FAX
6									
7									
8									J BNC JACK
9								S ARE IN INCHES	
10					DRAWN C. ZUNIGA	3/14/07	AND [MILLI	-	BULKHEAD, NO HARDWARE, ISOLATED RECEPTACLE
1 1					CHECKED	-,,		HERWISE NOTED	SIZE CABLE GROUP . DWG NO. REV
12					OI ILOINED		TOLERANCE	<u> </u>	
13					ORJ DRAWN	7/14/07	DECIMALS	DIAMETER	A N/A RFB-1716-I-03 -
14					C. ZUNIGA	3/14/07			CAD FILE
#	DESCRIPTION	QTY	MATERIAL	FINISH	APPROVALS	DATE			SCALE: NTS CAD FILE OUTLINE SHEET 1 OF 1