SIEMENS

Data sheet

3RA2120-0KA23-0BB4



Fuseless motor starter Direct start 600VAC Size S0 0.9-1.25A 24V DC screw connection For screw mounting Or 35 mm rail-mounting Type of coordination 2 IQ = 150 KA Also full fills type Of coordination 1 1NO+1NC (contactor)

product brand name	SIRIUS			
product designation	non-fused motor starter 3RA2			
design of the product	direct starter			
manufacturer's article number				
 of the supplied contactor 	3RT2023-1BB40			
 of the supplied circuit-breakers 	3RV2011-0KA10			
 of the supplied link module 	3RA2921-1BA00			
General technical data				
size of the circuit-breaker	S00			
size of load feeder	S0			
product extension auxiliary switch	Yes			
insulation voltage with degree of pollution 3 at AC rated value	690 V			
degree of pollution	3			
surge voltage resistance rated value	6 kV			
shock resistance according to IEC 60068-2-27	6g / 11 ms			
mechanical service life (switching cycles) of contactor typical	10 000 000			
type of assignment	2			
Substance Prohibitance (Date)	03/01/2017			
Ambient conditions				
ambient temperature				
 during operation 	-20 +60 °C			
 during storage 	-50 +80 °C			
 during transport 	-55 +80 °C			
Main circuit				
number of poles for main current circuit	3			
design of the switching contact	electromechanical			
adjustable current response value current of the current-dependent overload release	0.9 1.25 A			
operating voltage				
• rated value	690 V			
at AC-3 rated value maximum	690 V			
operating frequency rated value	50 60 Hz			
operational current at AC-3 at 400 V rated value	1.1 A			
operating power at AC-3				
• at 400 V rated value	370 W			
• at 500 V rated value	550 W			
• at 690 V rated value	750 W			
Control circuit/ Control				

control supply voltage at DC							
rated value		24 V					
holding power of magnet coil at DC		5.9 W					
Auxiliary circuit							
number of NC contacts for auxiliary conta		1					
number of NO contacts for auxiliary conta	acts	1					
Protective and monitoring functions							
trip class		CLAS					
design of the overload release			al (bimetallic)				
response value current of instantaneous sho unit	rt-circuit trip	16.25 A					
UL/CSA ratings							
full-load current (FLA) for 3-phase AC mo	tor						
 at 480 V rated value 		1.19 /	4				
at 600 V rated value		1.25	4				
yielded mechanical performance [hp]							
 for 3-phase AC motor 							
 at 460/480 V rated value 		0.5 hp)				
— at 575/600 V rated value		0.5 hp)				
Short-circuit protection							
product function short circuit protection		Yes					
design of the short-circuit trip		magn	etic				
conditional short-circuit current (Iq)							
 at 400 V according to IEC 60947-4-1 range 	ated value	153 0	00 A				
Installation/ mounting/ dimensions							
mounting position		vertic	al				
fastening method		Snap-	mounted to DIN rail or	screw-mounted with a	dditional push-in lug		
height		193.1	mm				
width		45 mr	n				
depth		107 m	nm				
required spacing							
 for grounded parts 							
— forwards		10 mr	n				
backwards		0 mm					
— upwards		30 mm					
— at the side		9 mm					
— downwards		10 mm					
 for live parts 							
— forwards		10 mr	n				
— backwards		0 mm					
— upwards		30 mr	30 mm				
— downwards		10 mm					
— at the side		9 mm					
Connections/ Terminals							
type of electrical connection for main current	circuit	screw	-type terminals				
type of connectable conductor cross-sect	tions						
 for main contacts stranded 		1 1	1 10 mm², 2x (2.5 6 mm²)				
at AWG cables for main contacts		2x (16	2x (16 12), 2x (14 8)				
connectable conductor cross-section for main finely stranded with core end processing	n contacts	1 6	1 6 mm²				
Safety related data							
B10 value with high demand rate according to SN 31920			1 000 000				
proportion of dangerous failures with high demand rate according to SN 31920		73 %					
protection class IP on the front according to IEC 60529		IP20					
touch protection on the front according to	DIEC 60529	finaer	-safe, for vertical conta	act from the front			
Certificates/ approvals		901	.,				
	For use in ha	7224	Doclaration of				
General Product Approval	ous locations		Declaration of Conformity	other	Dangerous Good		





Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2120-0KA23-0BB4

Cax online generator

 $\underline{\text{http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en\&mlfb=3RA2120-0KA23-0BB4}$

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RA2120-0KA23-0BB4

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)


http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2120-0KA23-0BB4&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RA2120-0KA23-0BB4/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2120-0KA23-0BB4&objecttype=14&gridview=view1



last modified: 12/15/2020 ☑