## SIEMENS

## Data sheet

## 3RA2210-0CA15-2BB4





Load feeder fuseless, Reversing duty 400 V AC, Size S00 0.18...0.25 A 24 V DC screw terminal for installation on standard mounting rail (also fulfills type of coordination 1) Type of coordination 2, Iq = 150 kA 1 NC (contactor)

product brand name	SIRIUS
product designation	Reversing starter
design of the product	for standard rail or screw mounting
product type designation	3RA22
manufacturer's article number	
<ul> <li>of the supplied contactor</li> </ul>	<u>3RT2015-1BB42</u>
<ul> <li>of the supplied circuit-breakers</li> </ul>	<u>3RV2011-0CA10</u>
<ul> <li>of the supplied link module</li> </ul>	<u>3RA1921-1DA00</u>
General technical data	
size of the circuit-breaker	S00
size of load feeder	S00
insulation voltage with degree of pollution 3 at AC rated value	690 V
surge voltage resistance rated value	6 kV
degree of protection NEMA rating	other
shock resistance according to IEC 60068-2-27	6g / 11 ms
mechanical service life (switching cycles) of contactor typical	30 000 000
type of assignment	2
type of protection according to ATEX directive 2014/34/EU	Ex II (2) GD
certificate of suitability according to ATEX directive 2014/34/EU	DMT 02 ATEX F 001
Substance Prohibitance (Date)	10/01/2009
Ambient conditions	_
ambient temperature	
<ul> <li>during operation</li> </ul>	-20 +60 °C
<ul> <li>during storage</li> </ul>	-50 +80 °C
during transport	-50 +80 °C
temperature compensation	-20 +60 °C
relative humidity during operation	10 95 %
Main circuit	
number of poles for main current circuit	3
design of the switching contact	electromechanical
adjustable current response value current of the current-dependent overload release	0.18 0.25 A
operating voltage	
<ul> <li>rated value</li> </ul>	690 V
<ul> <li>at AC-3 rated value maximum</li> </ul>	690 V
operating frequency rated value	50 60 Hz

operational current at AC-3 at 400 V rated value	0.2 A
operating power at AC-3	CO 144
• at 400 V rated value	60 W
Control circuit/ Control	20
type of voltage of the control supply voltage	DC
control supply voltage at DC	
rated value	24 V
• rated value	24 24 V
holding power of magnet coil at DC	4 W
Auxiliary circuit	
product extension auxiliary switch	Yes
Protective and monitoring functions	
trip class	CLASS 10
design of the overload release	thermal (bimetallic)
UL/CSA ratings	
full-load current (FLA) for 3-phase AC motor	
at 480 V rated value	0.25 A
Short-circuit protection	
product function short circuit protection	Yes
design of the short-circuit trip	magnetic
conditional short-circuit current (Iq)	
<ul> <li>at 400 V according to IEC 60947-4-1 rated value</li> </ul>	150 000 A
Installation/ mounting/ dimensions	
mounting position	vertical
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail
height	170 mm
width	90 mm
depth	97 mm
required spacing	
<ul> <li>for grounded parts</li> </ul>	
— forwards	32 mm
— backwards	0 mm
— upwards	50 mm
— at the side	10 mm
— downwards	10 mm
<ul> <li>for live parts</li> </ul>	
— forwards	32 mm
— backwards	0 mm
— upwards	50 mm
— downwards	10 mm
— at the side	10 mm
Connections/ Terminals	
type of electrical connection	
for main current circuit	screw-type terminals
<ul> <li>for auxiliary and control circuit</li> </ul>	screw-type terminals
type of connectable conductor cross-sections	
for main contacts	
— stranded	0.5 4 mm², 2x (0.75 2.5 mm²)
at AWG cables for main contacts	2x (20 16), only for contactor 2x (18 14), 2x 12
connectable conductor cross-section for main contacts finely stranded with core end processing	0.5 2.5 mm²
Safety related data	
B10 value with high demand rate according to SN 31920	1 000 000
proportion of dangerous failures	
with high demand rate according to SN 31920	73 %
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front
Communication/ Protocol	
protocol is supported	
PROFINET IO protocol	No
· · · · · · · · · · · · · · · · · · ·	

<ul> <li>PROFIsafe prof</li> </ul>	tocol	No				
protocol is supported		No				
Certificates/ approval						
General Product Ap				For use in hazard-	Declaration of	
contraining	,proval			ous locations	Conformity	
(SP)	<u>Confirmation</u>		EHC	K ATEX	CE EG-Konf.	
Declaration of Conformity	Test Certificates		Marine / Shipping			
UK CA	<u>Type Test Certific-</u> ates/Test Report	Special Test Certific- ate	ABS	B U RE A U VERITAS	Lloyd's Register uis	
Marine / Shipping				other	Railway	
PRS	RINA	RMRS	DNV-GL EWOLDENN	<u>Confirmation</u>	Vibration and Shock	
Dangerous Good						
Transport Informa- tion						
Further information						
Information- and Downloadcenter (Catalogs, Brochures,) https://www.siemens.com/ic10 Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2210-0CA15-2BB4						
Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2210-0CA15-2BB4 Service&Support (Manuals, Certificates, Characteristics, FAQs,) https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-0CA15-2BB4						
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2210-0CA15-2BB4⟨=en						
Characteristic: Tripping characteristics, I <sup>2</sup> t, Let-through current https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-0CA15-2BB4/char Further characteristics (e.g. electrical endurance, switching frequency) http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2210-0CA15-2BB4&objecttype=14&gridview=view1						





last modified:

